



Relays, Contactors & Switches > Relays > Power Relays



Power Relay Type: **Industrial Panel Plug-In**

Coil Magnetic System: **Monostable, AC**

Coil Power Rating Class: **[2 – 3 VA]**

Coil Power Rating AC: **1.96 VA, 2.32 VA**

Coil Resistance: **8300 Ω**

Features

Product Type Features

Power Relay Type	Industrial Panel Plug-In
------------------	--------------------------

Electrical Characteristics

Insulation Initial Dielectric Between Coil & Contact Class	1500 – 2500 V
Insulation Initial Dielectric Between Contacts & Coil	2500 Vrms
Actuating System	AC
Insulation Initial Dielectric Between Open Contacts	1500 Vrms
Contact Limiting Making Current	20 A
Contact Limiting Short-Time Current	10 A
Contact Limiting Continuous Current	10 A
Insulation Creepage Class	3 – 5.5 mm
Insulation Initial Dielectric Between Adjacent Contacts	2500 Vrms
Insulation Creepage Between Contact & Coil	4 mm[.157 in]
Contact Limiting Breaking Current	10 A
Coil Magnetic System	Monostable, AC
	2 – 3 VA
Coil Power Rating AC	1.96 VA, 2.32 VA
Coil Resistance	8300 Ω
Coil Special Features	Electrical Indicator, LED, UL Coil Insulation Class B



Coil Voltage Rating	230 VAC
Contact Switching Load (Min)	10mA @ 12V
Contact Switching Voltage (Max)	400 VAC
Contact Voltage Rating	240 VAC

Body Features

Product Weight	80 g[2.824 oz]
----------------	----------------

Contact Features

Contact Arrangement	2 Form C (CO)
Contact Current Class	5 – 10 A, 16 A
Contact Current Rating (Max)	10 A
Contact Material	AgNi90/10
Contact Number of Poles	2
Terminal Type	Plug-In

Mechanical Attachment

Relay Mounting Type	Socket
---------------------	--------

Dimensions

Length Class (Mechanical)	35 – 40 mm
Insulation Clearance Class	2.5 – 4 mm
Insulation Clearance Between Contact & Coil	2.8 mm[.11 in]
Width Class (Mechanical)	30 – 40 mm
Product Width	35.5 mm[1.398 in]
Product Length	35.6 mm[1.402 in]
Product Height	57 mm[2.244 in]

Usage Conditions

Environmental Ambient Temperature Class	0 – 50 °C
Environmental Ambient Temperature (Max)	50 °C[122 °F]
Operating Temperature Range	-40 – 50 °C

Packaging Features

Packaging Method	Box & Tray
------------------	------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: 4,4'-isopropylidenediphenol (Bisphenol A) (.3% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




TE Part # 8-1393163-4
MT78745



TE Part # 3-1415035-1
MT78755



TE Part # 7-1415043-1
MT78612



TE Part # 9-1415043-1
MT78602

Also in the Series | SCHRACK Multimode Relay MT



Power Relays(77)


Customers Also Bought



TE Part #1-749656-2
IDC D-Sub: Receptacle Assembly, Panel Mount, Signal, 1.27 mm




TE Part #1-1879452-7
Wirewound Resistor: Mineral, 2.5 Kw



TE Part #1-2308341-1
D-SUB BACKSHELL SIZE 2



TE Part #8-1393163-4
MT78745



TE Part #1-1415073-1
RT4S4LC4



TE Part #1622414-1
LR1 1% 2K2



TE Part #1622454-1
LR1 1% 390R



TE Part #1622386-1
LR1 1% 220R



TE Part #1-2308272-4
CABLE CLAMP FOR SIZE 1-3STD/1-4 QL SHELL



TE Part #1217176-1
CLUSTER BLOCK RECPT.

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_7-1393090-1_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_7-1393090-1_B.3d_igs.zip



English

Customer View Model

[ENG_CVM_CVM_7-1393090-1_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Accessories - Power Relay MT](#)

English

[Multimode Relay MT](#)

English

[Industrial Relays Quick Reference Guide](#)

English

[Industrial Relays Quick Reference Guide](#)

Japanese

[Industrial Relays Quick Reference Guide](#)

Product Specifications

[Definitions, Handling, Processing, Testing and Use of Relays](#)

English

Agency Approvals

[VDE Certificate](#)

English