

KUHP-11DT1-12

✓ ACTIVE

Potter & Brumfield | Potter & Brumfield KUHP

TE Internal #: 7-1393114-2

Potter & Brumfield KUHP, Power Relays, Industrial Panel Plug-In,
Monostable, DC, 1000 – 1500mW Coil Power Rating Class, 1200mW
Coil Power Rating DC

[View on TE.com >](#)



Relays, Contactors & Switches > Relays > Power Relays



Power Relay Type: **Industrial Panel Plug-In**
Coil Magnetic System: **Monostable, DC**
Coil Power Rating Class: **1000 – 1500 mW**
Coil Power Rating DC: **1200 mW**
Coil Resistance: **120 Ω**

Features

Product Type Features

Power Relay Type	Industrial Panel Plug-In
------------------	--------------------------

Electrical Characteristics

Insulation Initial Dielectric Between Coil & Contact Class	3500 – 4000 V
Insulation Initial Dielectric Between Contacts & Coil	3750 Vrms
Actuating System	DC
Insulation Initial Dielectric Between Open Contacts	1200 Vrms
Contact Limiting Making Current	20 A
Contact Limiting Short-Time Current	20 A
Contact Limiting Continuous Current	20 A
Insulation Initial Dielectric Between Adjacent Contacts	3750 Vrms
Insulation Initial Resistance	100 M Ω
Contact Limiting Breaking Current	20 A
Coil Magnetic System	Monostable, DC
Coil Power Rating Class	1000 – 1500 mW
Coil Power Rating DC	1200 mW
Coil Resistance	120 Ω
Coil Special Features	UL Coil Insulation Class B
Coil Voltage Rating	12 VDC



Contact Switching Load (Min)	300mA @ 12V
Contact Voltage Rating	240 VAC

Body Features

Product Weight	92 g[3.245 oz]
----------------	----------------

Contact Features

Contact Arrangement	2 Form C (CO)
Contact Current Class	10 – 20 A, 16 A
Contact Current Rating (Max)	20 A
Contact Material	AgCdO
Contact Number of Poles	2
Terminal Type	Quick Connect, Solder

Mechanical Attachment

Relay Mounting Type	Flange Mount, Panel Mount
---------------------	---------------------------

Dimensions

Length Class (Mechanical)	35 – 40 mm
Width Class (Mechanical)	30 – 40 mm
Product Width	35.4 mm[1.394 in]
Product Length	38.1 mm[1.5 in]
Product Height	62.5 mm[2.461 in]

Usage Conditions

Environmental Ambient Temperature Class	50 – 70 °C
Environmental Ambient Temperature (Max)	70 °C[158 °F]
Operating Temperature Range	-45 – 70 °C

Packaging Features

Packaging Method	Package
------------------	---------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	



Current ECHA Candidate List: JAN 2021
(211)
Candidate List Declared Against: JAN 2021
(211)
SVHC > Threshold:
Cadmium oxide (5.1% in Component Part)
Article Safe Usage Statements:
Use personal protective equipment as required. Do not eat, drink or smoke when using this product. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 7-1393114-7
KUHP-11D51-12=KU


Also in the Series | Potter & Brumfield KUHP

Power Relays(31)

Customers Also Bought




TE Part #M3041-000005-05KPG
Pressure Transducers Readily Available



TE Part #1-6609028-3
CORCOM K SERIES SINGLE PHASE FILTERS



TE Part #1-770250-0
UMNL II PIN SN/AUNI/BR LP20-14



TE Part #1761608-5
IDC LOW PRO HDR 14P VERT SHT L




TE Part #1393143-1
27E043=SOCKET,KU,11,SLG,NYL,N



TE Part #1419111-6
24A110=TRACK,MOUNTING



TE Part #1437624-8
PK70B1/4=KNOB PLASTIC BLK 1/4



TE Part #1-1676814-4
Power Resistors: Aluminum Housed, HSA



TE Part #1-770008-0
UMNLII SOK SN/AU/PHBZ LF



TE Part #1393771-4
JWD-107-3=REED RELAYS

Documents

CAD Files

Customer View Model

ENG_CVM_7-1393114-2_0303.3d_igs.zip

English

Customer View Model

ENG_CVM_7-1393114-2_0303.3d_stp.zip

English

Customer View Model

ENG_CVM_7-1393114-2_0303.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

KUHP 30 Amp Power Relays

English

Industrial Relays Quick Reference Guide



English

[Industrial Relays Quick Reference Guide](#)

Japanese

[Industrial Relays Quick Reference Guide](#)

Product Specifications

[Definitions, Handling, Processing, Testing and Use of Relays](#)

English