



Relays, Contactors & Switches > Relays > Time Delay Relays



Type of Control: **Knob**

Time Delay Relay Input Voltage: **125 VDC**

Time Delay Relay Contact Current Rating: **10A@240VAC A**

Mode of Operation: **On-Delay**

Delay Time: **30 – 300 seconds**

## Features

### Product Type Features

Product Type	Relay
Relay Type	Time Delay
Product Category	Electromechanical Relays
Magnetic Blow-Out Device	Without

### Configuration Features

Multiple Timing Ranges	Without
------------------------	---------

### Electrical Characteristics

Actuating System	DC
Time Delay Relay Input Voltage	125 VDC

### Contact Features

Contact Arrangement	4 Form C, 4PDT, 4 C/O
Type of Control	Knob
Time Delay Relay Contact Current Rating	10A@240VAC A
Delay Time	30 – 300 seconds

### Termination Features

Termination Type	Screw Terminals
------------------	-----------------

### Mechanical Attachment



Time Delay Relay Mounting Type

Mounting Bracket

### Dimensions

Dimensions (L x W x H) (Approximate)

147.82 x 82.55 x 84.32 mm[5.82 x 3.25 x 3.32 in]

### Usage Conditions

Operating Temperature Range

-30 – 75 °C

### Operation/Application

Option

Two Auxiliary Switches - Instant Transfer

Mode of Operation

On-Delay

### Other

Repeatability (Max)

±10%

## Product Compliance

For compliance documentation, visit the product page on [TE.com](https://www.te.com)>

EU RoHS Directive 2011/65/EU

Not Compliant

EU ELV Directive 2000/53/EC

Not Compliant

China RoHS 2 Directive MIIT Order No 32, 2016

Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JAN 2021 (211)  
Candidate List Declared Against: JAN 2021 (211)  
Does not contain REACH SVHC

Halogen Content

Not Yet Reviewed for halogen content

Solder Process Capability

Not applicable for solder process capability

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

## Compatible Parts



TE Part # 2-1423159-6  
7012PD=RLY,STD,ON,2P,125VDC,50

## Also in the Series | Agastat 7000



Pre-Printed Markers(888)



Time Delay Relays(214)

## Customers Also Bought



TE Part #1-1423157-2  
7012AE=RLY,STD,ON,2P,120VAC,20



TE Part #5413589-2  
KIT PLUG 75 OHM BNC HEX CRIMP



TE Part #4-1393104-4  
KRPA-11DG-125=KRPA



TE Part #1SNK900001R0000  
BAM4



TE Part #2-1423159-6  
7012PD=RLY,STD,ON,2P,125VDC,50




TE Part #1SNA105053R2200  
M4/6.SNB



TE Part #1SNA115277R2000  
M6/8.STP



TE Part #1SNA115529R1500  
M6/8.STP1



## Documents

### Product Drawings

[7014PELL=RLY,STD,ON,4P,125V,200S,LL](#)

English

### Datasheets & Catalog Pages

[5-1773450-5\\_sec12\\_7000](#)

English