



Relays, Contactors & Switches > Switches > Push Button Switches



Configuration (Pole-Throw): **Four Pole - Double Throw**

Push Button Switch Product Type: **Switch**

Number of Actuators: **Single**

Actuator Profile: **Extended**

Bushing Style: **Threaded**

Features

Product Type Features

Switch Type	Pushbutton
Dust Proof	No
Push Button Switch Product Type	Switch
Illuminated	No
Actuator Style	Cap - Supplied

Configuration Features

ESD Grounding Terminal	Without
Ganged	No
Configuration (Pole-Throw)	Four Pole - Double Throw
Number of Actuators	Single
Snap Action	Without
Support Bracket	Without
Tactile	No
Operating Function	Push-On/Push-Off

Electrical Characteristics

Push Button Switch Voltage Rating	28 VDC
-----------------------------------	--------

Body Features

Actuator Force	590 – 1224 g[20.8 – 43.18 oz]
----------------	-------------------------------



Case Material	Thermoset
Actuator Material	Phenol Resin
Actuator Profile	Extended
Bushing Style	Threaded
Bushing Thread Size	15/32
Actuator Color	Natural

Contact Features

Contact Base Material	Silver Clad Copper
Push Button Switch Contact Current Rating	6 A
Switch Contact Plating Material	Silver Clad with Gold Flash

Termination Features

Termination Type	Wire Lugs
------------------	-----------

Mechanical Attachment

Mounting Angle	Vertical
Screw & Hole Thread Size	15/32-32 UNS-2A
Push Button Switch Mounting Type	Panel

Housing Features

Low Profile	No
Process Sealed	No

Dimensions

Cap Height	3.5 mm[.138 in]
Actuator Length	8 mm[.315 in]
Cap Diameter	8.99 mm[.354 in]

Usage Conditions

Temperature Rating	Standard
--------------------	----------

Packaging Features

Packaging Method	Bulk
------------------	------

Other

Comment	Black cap is supplied., Other cap colors available (cap model C9).
---------	--

Product Compliance

For compliance documentation, visit the product page on TE.com>



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (3.7% in component) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 240°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 4-1437567-9 MPG106D=(MSPG) SWITCH PUSHBUTT	 TE Part # 3-1437567-3 MPA206R=SW P/B MOM DPDT	 TE Part # 4-1437567-3 MPE106F=SWITCH PUSH BUTTON WAT	 TE Part # 4-1437567-5 MPE206R=(MSPE) SW P/B WATERPRO WAT
---	---	---	---



TE Part # 2-1437567-9
MPA106F=SWITCH P/B MOM SPDT

Also in the Series | Alcoswitch MPG

Push Button Switches(10)

Customers Also Bought

TE Part #1-66504-0
D-Sub Conn Contacts: Socket, Phosphor Bronze, Signal, Size 20

TE Part #1-2308341-3
D-SUB BACKSHELL SIZE 2

TE Part #1558662-2
PCB Power Relay: 30 amp, Monostable DC

TE Part #1-2176089-4
RP 1J 0.166W 14K7 0.1% 25PPM 1K RL

TE Part #1-796949-8
18POS TERMI-BLOK PCB MOUNT

TE Part #1-2176372-8
RQ 0603 75K 0.1% 10PPM 5K RL

TE Part #1-2176381-5
RQ 0805 17K4 0.1% 10PPM 5K RL

TE Part #9-1879131-2
RN 0402 12K1 0.1% 10PPM 1K RL

TE Part #1-1423673-8
W51-A151A1-15=CKTBKR,THERM, ROC

TE Part #1-1393250-7
W28-XQAT-15=W28



Documents

Product Drawings

MPG406N=(MSPG) SW PUSHBUTTON

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_5-1437567-7_D.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_5-1437567-7_D.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_5-1437567-7_D.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

2-1773458-6_GREEN_SERIES_SWITCHES

English