



TERMI-FOIL | TERMI-FOIL


TE Internal #: 51943

TERMI-FOIL, Foil Terminals, End Tap, Type 13, Foil Terminal Tab

Width .25 in [6.35 mm], Foil Thickness (Max) .03 in [.76 mm], Tin, Box

[View on TE.com >](#)

Terminals & Splices > Foil Terminals



Foil Terminal Terminal Type: **End Tap**

Body Type: **Type 13**

Foil Terminal Tab Width: **6.35 mm [.25 in]**

Foil Thickness (Max): **.76 mm [.03 in]**

Foil Terminal Plating Material: **Tin**

Features

Product Type Features

Insulated	No
-----------	----

Body Features

Face	Double
Body Type	Type 13
Foil Terminal Plating Material	Tin

Contact Features

Foil Terminal Terminal Type	End Tap
-----------------------------	---------

Termination Features

Foil Thickness (Max)	.76 mm[.03 in]
----------------------	----------------

Dimensions

Foil Terminal Tab Width	6.35 mm[.25 in]
-------------------------	-----------------

Usage Conditions

Insulation Requirement	Uninsulated
Operating Temperature Range	150 °C[302 °F]

Packaging Features

Packaging Quantity	100
Foil Terminal Packaging Method	Box

Other

Comment	Accepts 6.35 [.250] FASTON Tab.
---------	---------------------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts



Also in the Series | TERMI-FOIL



Customers Also Bought



Documents

Product Drawings
TAB, TERMI-FOIL END TAP TERMINAL
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_51943_G.2d_dxf.zip
English
Customer View Model
ENG_CVM_CVM_51943_G.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_51943_G.3d_stp.zip
English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Instruction Sheets
PRE-SET HAND TOOL,TERMI-FOIL
Japanese
Instruction Sheet (non U.S.)
Japanese