




Raychem

TE Internal #: 752055-000

Heat Shrink Boots, 90°, Molded Part Shape Code 222, Lipped, 51, 20, Adhesive Pre-Coat, Operating Temperature Range -55 – 135 °C [-67 – 275 °F]

[View on TE.com >](#)

Wire Protection & Management > Heat Shrink Molded Shapes > Heat Shrink Boots > Low Profile Heat Shrink Boots: Blow Mold, Lipped, Right Angle



Molded Part Shape: 90°

Molded Part Shape Code: 222

Lipped: Yes

Material Code: 51

Heat Shrink Boot Material Systems Code: 20

[All Low Profile Heat Shrink Boots: Blow Mold, Lipped, Right Angle \(51\)](#)

Features

Product Type Features

Molded Part Shape	90°
-------------------	-----

Configuration Features

Lipped	Yes
--------	-----

Body Features

Material Code	51
Heat Shrink Boot Material Systems Code	20
Adhesive Pre-Coat	Yes
Material	Modified Fluoro-Elastomer

Dimensions

Inside Diameter as Supplied	24 mm[.945 in]
Cable Diameter Range	9.9 – 23.9 mm[.39 – .94 in]

Usage Conditions

Operating Temperature Range	-55 – 135 °C[-67 – 275 °F]
-----------------------------	----------------------------

Operation/Application

Power Cable Accessory	No
-----------------------	----

Industry Standards



Approved Standards	SC-X-15112
Government Qualified	No

Other

Molded Part Shape Code	222
Fluid/Chemical Resistance	Suitable for long term fluid immersion & elevated temperatures including fuel

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CJ2087-000
HL2010E-KIT-120V

Customers Also Bought



TE Part #206486-1
CPC SERIES 2



TE Part #323916
PIDG RING TONGUE TERMINALS




TE Part #0660-206-1631L
CONT PIN



TE Part #199339-000
Low Profile HS Boots: Blow Molded,
Slim Line, Lipped, Straight



TE Part #YDTS24F17-35SAV001
D38999: Jam Nut, 17-35 Insert



TE Part #445160-000
0022E0311-9



TE Part #2-1616980-5
K200A1C1=CONTACTOR 200 AMP
SPST 28 VDC



TE Part #2-1617029-3
HFW1131D00 = HFW 1/2 SIZE RELA



TE Part #1617352-5
JMSC-26XLS=M39016/11-044L

Documents

[Product Drawings](#)
222F211-51-22/164-0

English

[Datasheets & Catalog Pages](#)
1654025_Sec4_-51

English

[Raychem Molded Parts Visual Guide](#)

English

222F211-51-22/164-0

Heat Shrink Boots, 90°, Molded Part Shape Code 222, Lipped, 51, 20, Adhesive Pre-Coat, Operating Temperature Range -55 – 135 °C [-67 – 275 °F]

