222A152-4/86-0 ✔ ACTIVE


Raychem

TE Internal #: 769185-000

Heat Shrink Boots, 90°, Molded Part Shape Code 222, 4, 10, Adhesive Pre-Coat, Operating Temperature Range -55 – 135 °C [-67 – 275 °F]

View on TE.com >

Wire Protection & Management > Heat Shrink Molded Shapes > Heat Shrink Boots > Heat Shrink Boots: Non Lipped, Right Angle



Molded Part Shape: **90°**

Molded Part Shape Code: **222**

Lipped: **No**

Material Code: **4**

Heat Shrink Boot Material Systems Code: **10**

All Heat Shrink Boots: Non Lipped, Right Angle (136)

Features

Product Type Features

Molded Part Shape	90°

Configuration Features

Lipped	No

Body Features

Material Code	4
Heat Shrink Boot Material Systems Code	10
Adhesive Pre-Coat	Yes
Material	Polyolefin Flexible Modified

Dimensions

Wire/Cable Outside Diameter	.39 in, .43 in, .433 in, .47 in, .55 in, .63 in, 10 mm, 11 mm, 12 mm, 14 mm, 16 mm
Cable Diameter Range	8.4 – 26.4 mm[.331 – 1.039 in]

Usage Conditions

Operating Temperature Range	-55 – 135 °C[-67 – 275 °F]

Operation/Application

Power Cable Accessory	No

Industry Standards

Approved Standards	SAE AS I 81765/1, Type II, UL 224, File E85381
Government Qualified	No

Other

Molded Part Shape Code	222
Fluid/Chemical Resistance	Occasional exposure to fluids
Adhesive Type	High Performance Pre-Coat Adhesive

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts




TE Part # CJ2087-000
HL2010E-KIT-120V


Customers Also Bought



TE Part #205557-2
RECEPT ASSY,15 POSN,AMPLIMITE



TE Part #1742898-1
AMVAR SPLC 10M-22M 0295 TPBR



TE Part #172079-000
Bulbous Heat Shrink Boots: Lipped, Straight



TE Part #2-31880-1
PIDG RING TONGUE TERMINALS




TE Part #YDTS26F17-35PCV001
Straight Plug: D38999, 17-35 Insert, Electroless Nickel Plating




TE Part #1490599-1
HYP10 TERMINYL 4AWG DIE SET



TE Part #1490597-1
HYP10 TERMINYL 8AWG DIE SET



TE Part #1-446080-0
BOX 4 ROW R/A PIN ASSY 200 POS



TE Part #1-446081-0
BOX 4 ROW ASSY 200 POS



TE Part #118239-000
55A4832-20-MST3-9CS2275

Documents

Datasheets & Catalog Pages

1654025_Sec4_-4

English

Raychem Molded Parts Visual Guide

English

Product Specifications

Product Specification

English

Product Environmental Compliance

Safety Datasheet

Safety Datasheet

German

Safety Datasheet

German

Safety Datasheet

English

Safety Datasheet

English

Safety Datasheet

English

Safety Datasheet

Safety Datasheet

French

Safety Datasheet

French

Safety Datasheet

Safety Datasheet

Safety Datasheet

Safety Datasheet

Safety Datasheet

Safety Datasheet