202G632-55-0 ✔ ACTIVE


Raychem

TE Internal #: 769563-000

Heat Shrink Boots, 180˚, Molded Part Shape Code 202, Lipped, 55, 300, Operating Temperature Range -65 – 200 °C [-85 – 392 °F]

View on TE.com >

Wire Protection & Management > Heat Shrink Molded Shapes > Heat Shrink Boots > Convoluted Heat Shrink Uni Boots: Lipped, Straight



Molded Part Shape: **180˚**

Molded Part Shape Code: **202**

Lipped: **Yes**

Material Code: **55**

Heat Shrink Boot Material Systems Code: **300**

All Convoluted Heat Shrink Uni Boots: Lipped, Straight (67)

Features

Product Type Features

Molded Part Shape	180˚

Configuration Features

Lipped	Yes

Body Features

Material Code	55
Heat Shrink Boot Material Systems Code	300
Adhesive Pre-Coat	No
Material	Flexible Fluoropolymer

Dimensions

Wire/Cable Outside Diameter	.55 in, .63 in, .7 in, .71 in, .787 in, .87 in, 14 mm, 16 mm, 18 mm, 20 mm, 22 mm
Cable Diameter Range	13.2 – 29 mm[.52 – 1.142 in]

Usage Conditions

Operating Temperature Range	-65 – 200 °C[-85 – 392 °F]
Flammability	Flame-Retardant

Operation/Application

Power Cable Accessory	No

Industry Standards

Approved Standards	None
Government Qualified	No

Other

Molded Part Shape Code	202
Fluid/Chemical Resistance	Long-Term Exposure at High Temperature
Adhesive Options	S1255-04 Separate Adhesive
Adhesive Type	Adhesive Purchased Separately

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts




TE Part # 195133-000
S1255-04-3/4X100FT




TE Part # CJ2087-000
HL2010E-KIT-120V


Customers Also Bought



TE Part #806424-000
Slim Line Heat Shrink Boots: Non Lipped, Straight




TE Part #819101-000
301A512-51-0



TE Part #720633-000
301A511-51/164-0



TE Part #483859-000
TXR15AB00-1008AI



TE Part #138458-000
TXR54AB90-0804AI



TE Part #806808-000
234A011-25-0



TE Part #YDTS26Z13-98PNV001
D38999: Straight Plug, 13-98 Insert



TE Part #445160-000
0022E0311-9



TE Part #180321-000
2022E0421-9X



TE Part #618529-000
55A0823-20-9/96CS2275

Documents

Product Drawings

202G632-55-0

English

Datasheets & Catalog Pages

1654025_Sec4_-55

English

Raychem Molded Parts Visual Guide

English

Product Specifications

Thermofit Fluoropolymer Molded Components Modified Flouropolymer, Radiation Crosslinked, Flexible, Abrasion Resistant, Flame Retarded, Heat-Shrinkable

English