



Application Tooling > Portable Crimp Tools



Tool Grade: **Commercial Crimp Tooling**
Ratchet Configuration: **Operator Releasable & Adjustable**
Die Sets Type: **Removable/Interchangeable**
TE Certification: **Cannot be Certified**
Power Technology Type: **Manual**

Features

Other

Crimp Form-Wire Barrel Type	Closed Barrel - Tetra
Tool Grade	Commercial Crimp Tooling
Ratchet Configuration	Operator Releasable & Adjustable
Die Sets Type	Removable/Interchangeable
TE Certification	Cannot be Certified
Power Technology Type	Manual
Tooling Type	PRO-CRIMPER Hand Tool

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content



Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # CAT-P592-R472A PIDG RING TONGUE TERMINALS	 TE Part # 8-320665-1 PG SPD 22-16 COMM 22-18 MIL 6	 TE Part # 2-320665-1 PG SPD 22-16 COMM 22-18 MIL 6	 TE Part # 8-34166-1 TERMINAL,PG SPD 16-14 8
 TE Part # 2-34166-1 TERMINAL,PG SPD 16-14 8	 TE Part # 34166 TERMINAL,PG SPD 16-14 8	 TE Part # 320665 PG SPD 22-16 COMM 22-18 MIL 6	 TE Part # 34854 TERMINAL,PG R 12-10 10
 TE Part # 8-34854-1 TERMINAL,PG R 12-10 10	 TE Part # 2-34854-1 TERMINAL,PG R 12-10 10	 TE Part # 1SET131006R0000 SD025-040-V	

Customers Also Bought



 TE Part #1658652-1 D-Sub Crimp: Plug, Signal, 50 Posn, Pin Size 20, Shell Size 5	 TE Part #1-1630186-9 Power Resistors: Aluminum Housed, HSA	 TE Part #1-534237-3 15 MODII VRT SR CE 100/115	 TE Part #1059733-1 4584 2244 02
 TE Part #11029075-00 PIEZOELECTRIC POLYMER VIBRATION SENSOR	 TE Part #NB-PTCO-295 RTD Platinum Thin Film Element	 TE Part #1-350766-1 03P UMNL V0 PLUG HSG BROWN	 TE Part #12333-12 CONT T.12 FEMELLE 1500 (SEE 182- 0447-12)
 TE Part #1925221-9 TMN2N009SC2DM018T = M32139/04- A05TNS	 TE Part #1-971111-2 9W FRC MADISON SPEC 100-4703 REV. 7		

Documents

Datasheets & Catalog Pages

1-1773865-2_1015_Commercial Manual Hand Tools

English

Crimp Term Whitepaper-Use the Right Tool 1-1773953-1

English

Bottoming Dies

English

CRIMPING WHERE FORM MEETS FUNCTION

English

Instruction Sheets

Instruction Sheet (U.S.)

English