



Product Compliance


[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2018 (191) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 1393143-6
27E122=SOCKET,KRP,8,SCW,PLES




TE Part # 2-1419106-3
27E891=SOCKET,KRPA,8,OCTAL,POL

Also in the Series | Potter & Brumfield KRPA




Power Relays(60)




Relay Accessories, Sockets & Clips(5)


Customers Also Bought



TE Part #1393143-6
27E122=SOCKET,KRP,8,SCW,PLES



TE Part #2-1419106-3
27E891=SOCKET,KRPA,8,OCTAL,POL




TE Part #102156-8
AMP-LATCH UNIVERSAL HEADERS



TE Part #9-1879517-3
CRGH1206 1% 39R 0.5W



TE Part #2-1393154-0
PT580110



TE Part #1-644487-0
Polyester Vertical PCB Header: 2.54 mm, Shrouded, MTA 100



TE Part #1825219-6
TT11EGPC104



TE Part #1044570-1
SCD,1064 5005 00,SSMA



TE Part #1393102-4
KRP-14DG-12=KA/KB/KC/KR



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_8-1393101-6_D.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_8-1393101-6_D.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_8-1393101-6_D.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

KRPA, KRP, KA, KR 5 to 10 Amp General Purpose Relay

English

Industrial Relays Quick Reference Guide

English

Industrial Relays Quick Reference Guide

Japanese

Industrial Relays Quick Reference Guide

Product Specifications

Definitions, Handling, Processing, Testing and Use of Relays

English