

RNF-3000-1.5/0.5-X-STK

✓ ACTIVE

Raychem | Raychem RNF-3000

TE Internal #: 5677902003

Raychem RNF-3000, Heat Shrink Tubing, Clear, Single Wall Type,
1.5 Expanded Inside Diameter (Min) .06 Expanded Inside Diameter
(Min)

[View on TE.com >](#)



Heat Shrink Tubing > RNF-3000 Single Wall Stick Heat Shrink



Primary Product Color: **Clear**

Wall Type: **Single**

Expanded Inside Diameter (Min): **1.5 mm [.06 in]**

Recovered Inside Diameter (Max): **.5 mm [.019 in]**

Shrink Ratio: **3:1**

[All RNF-3000 Single Wall Stick Heat Shrink \(180\)](#)

Features

Product Type Features

Product Family	RNF-3000
Wall Type	Single

Electrical Characteristics

Voltage (Max)	.6 kV
---------------	-------

Body Features

Fluid Type	Gasoline, Hydraulic Fluid, Lubricating Oil
Primary Product Color	Clear
Shrink Ratio	3:1
Primary Product Material	Irradiated Modified Polyolefin
Flexibility	Flexible

Dimensions

Recovered Wall Thickness (Tolerance)	.1 mm[.003 in]
Cut Length	1220 mm[48.03 in]
Recovered Wall Thickness (Nominal)	.45 mm[.018 in]
Expanded Inside Diameter (Min)	1.5 mm[.06 in]
Recovered Inside Diameter (Max)	.5 mm[.019 in]
Heat Shrink Tubing Size Range	.5 – 1.5 mm[.019 – .06 in]



Usage Conditions

Fluid Resistance	Splash Protection
Shrink Temperature (Min)	80 °C
Heat Shrink Tubing Flammability	Non-Flame-Retardant
Operating Temperature Range	-55 – 135 °C
Heat Shrink Tubing Resistance	Abrasion, Fluids, Mechanical Damage, Strain
Recovery Temperature	120 °C

Product Availability

Applicable Region	Global
-------------------	--------

Packaging Features

Packaging Method	Box
------------------	-----

Other

Meets Low Outgassing Requirements	No
Product Source	Czech Republic

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous



materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CJ2087-000
HL2010E-KIT-120V



TE Part # EG1114-000
CV1981-ST-230V1600W-EU

Also in the Series | Raychem RNF-3000



Heat Shrink Tubing(212)

Customers Also Bought



TE Part #1-338096-1
CRIMP CONTACTS



TE Part #1-163088-0
TYPE III CONTACTS LP EMEA




TE Part #2176362-4
RQ 0402 43R2 0.1% 10PPM 5K RL



TE Part #1879497-5
CRGH1206 5% 1R5 0.5W



TE Part #1337810-3
50 OHM COAX SMA STR PLUG ELB P



TE Part #160773-6
PL LOOSE PIECE REC 0.5-1.5 MM2 PTPBR



TE Part #1394475-1
MAG MATE ST-KONT2,0



TE Part #2160393004
55A0111-28-9

RNF-3000-1.5/0.5-X-STK

Raychem RNF-3000, Heat Shrink Tubing, Clear, Single Wall Type, 1.5 Expanded Inside Diameter (Min) .06 Expanded Inside Diameter (Min)



Documents

Product Drawings

RNF-3000-1.5/0.5-X-STK

English

Datasheets & Catalog Pages

RNF-3000 Pages from 9-1773447-9

English

Application Tooling for Raychem Heat Shrink Product

English

Product Specifications

Quality Specification

English