



Application Tooling > Portable Crimp Tools



Tool Grade: **Commercial Crimp Tooling**
Die Sets Type: **Removable/Interchangeable**
Specification Type: **TE Product Specification (114-), UL/CSA**
TE Certification: **Upon Request for Fee**
Power Technology Type: **Battery, Electric, Manual**

Features

Other

Crimp Form-Wire Barrel Type	Closed Barrel - Confined Crescent
Tool Grade	Commercial Crimp Tooling
Die Sets Type	Removable/Interchangeable
Specification Type	TE Product Specification (114-), UL/CSA
TE Certification	Upon Request for Fee
Power Technology Type	Battery, Electric, Manual
Tooling Type	PRO-CRIMPER Hand Tool

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2018 (181) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content






Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.











Compatible Parts

 <p>TE Part # 3-520151-2 ULTRAFAST 187 ASSY REC 16-14 TPBR LP</p>	 <p>TE Part # 2-520084-2 ULTRAFAST 110 ASSY REC 22-18 TPBR LP</p>	 <p>TE Part # 2-520081-2 ULTRAFAST 110 ASSY REC 22-18 TPBR LP</p>	 <p>TE Part # 2-520273-2 ULTRAFAST 110 ASSY REC 22-18 TPBR LP</p>
 <p>TE Part # 2-520182-2 ULTRAFAST 187 ASSY REC 22-18 TPBR LP</p>	 <p>TE Part # 2-520184-4 ULTRAFAST 250 ASSY REC 22-18 TPBR LP</p>	 <p>TE Part # 2-521103-2 ULTRA-FAST 187 ASY REC 22-18 TPBR</p>	 <p>TE Part # 2-521105-2 ULTRA-FAST 187 ASY REC 22-18 TPBR</p>
 <p>TE Part # 3-520117-2 ULTRAFAST 250 ASSY REC 16-14 TPBR LP</p>	 <p>TE Part # 3-520125-2 ULTRAFAST 187 ASSY REC 16-14 TPBR LP</p>	 <p>TE Part # 2-520264-2 ULTRAFAST 250 ASSY REC 22-18 TPBR LP</p>	 <p>TE Part # 2-520262-2 ULTRAFAST 187 ASSY REC 22-18 TPBR LP</p>



 <p>TE Part # 7-520366-2 ULTRAFAST 110 ASSY REC 26-22 TPBR LP</p>	 <p>TE Part # 2-520310-2 ULTRA-FAST .110/.125 ASY REC 22-18 TPBR</p>	 <p>TE Part # 2-521406-2 205 ULTRA-FAST RCPT 22-18 TPBR</p>	 <p>TE Part # 7-520365-2 ULTRA-FAST .110/.125 ASY REC 26-22 TPBR</p>
 <p>TE Part # 2-520306-2 ULTRA-FAST .110/.125 ASY REC 22-18 TPBR</p>	 <p>TE Part # 2-521104-2 ULTRA-FAST 187 ASY REC 22-18 TPBR</p>	 <p>TE Part # 2-521102-2 ULTRA-FAST 187 ASY Tab 22-18 TPBR</p>	 <p>TE Part # 3-520276-2 ULTRA-FAST 187 ASY REC 16-14 AWG TPBR</p>

Customers Also Bought

 <p>TE Part #1658681-1 D-Sub Crimp Recpt Signal 15 Posn, Socket Size 22, Shell Size 1</p>	 <p>TE Part #1658670-2 D-Sub Connector Contacts: Pin, Brass, Signal, Size 22</p>	 <p>TE Part #2-323758-1 PIDG RING TONGUE TERMINALS</p>	 <p>TE Part #1408313-1 MMCX Connector: Male (Jack)</p>
 <p>TE Part #102387-1 10 MODIV HSG COMP DR .100 POL</p>	 <p>TE Part #2-520084-2 ULTRAFAST 110 ASSY REC 22-18 TPBR LP</p>	 <p>TE Part #2-520182-2 ULTRAFAST 187 ASSY REC 22-18 TPBR LP</p>	 <p>TE Part #2-520103-2 ULTRA-FAST 250 ASSEMBLY TAB 22- 18 AWG BR</p>
 <p>TE Part #104257-2 03 MTE RCPT HSG SR LATCH .100</p>	 <p>TE Part #91508-1 CCII UNML UNML II PIN SKT 20-18 ASSY</p>		

Documents



Datasheets & Catalog Pages

1-1773865-2_1015_Commercial Manual Hand Tools

English

Crimp Term Whitepaper-Use the Right Tool 1-1773953-1

English

Bottoming Dies

English

CRIMPING WHERE FORM MEETS FUNCTION

English

Instruction Sheets

Instruction Sheet (U.S.)

English