




Wire Protection & Management > Interconnect Devices > SolderSleeve Shield Terminators



SolderSleeve Shield Terminator Product Type: **Shield Terminator**

SolderSleeve Shield Terminator Operating Temperature (Max): **150 °C**

SolderSleeve Shield Terminator Expanded Inside Diameter (Min): **5.08 mm [ .2 in ]**

SolderSleeve Shield Terminator Recovered Inside Diameter (Max): **2.16 mm [ .085 in ]**

Pre-Installed Lead: **Yes**

Features

Product Type Features

Temperature Indicator	Yes
Temperature Indicator Type	Thermochromic
SolderSleeve Shield Terminator Product Type	Shield Terminator

Configuration Features

Pre-Installed Lead Type	Braid Strap 654
Pre-Installed Lead	Yes

Dimensions

Overall Length	16.5 mm[.65 in]
Shield Outside Diameter (Min)	2.15 mm[.085 in]
Jacket Outside Diameter	5.08 mm[.2 in]
SolderSleeve Shield Terminator Expanded Inside Diameter (Min)	5.08 mm[.2 in]
SolderSleeve Shield Terminator Recovered Inside Diameter (Max)	2.16 mm[.085 in]

Usage Conditions

SolderSleeve Shield Terminator Operating Temperature (Max)	150 °C
Resistance Properties	Splash Protection
Wire Temperature (Max)	125 °C

Industry Standards

MIL/NAS Specification (MIL-S-83519, NAS-1747)	Yes
---	-----



Government Qualified

No

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (37% in Solder) <b>Article Safe Usage Statements:</b> Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CJ2087-000  
[HL2010E-KIT-120V](#)

Customers Also Bought




TE Part #324045  
TERMINAL,T-N R 8 3/8



TE Part #162927-000  
55A1121-16-9/96-9CS2275



TE Part #325411-000  
55A1121-20-9/96-9CS2275



TE Part #324693  
SPARE WIRE CAP,NAT, .048-.075 INS.,  
MOIS



TE Part #1052178-1  
SMA RIGHT ANGLE CABLE PLUG  
2037 8052 92




TE Part #504777-000  
55A4121-20-9/96-9CS2275




TE Part #YDTS20W15-35PDV001  
D38999: Square Flange, 15-35 insert



TE Part #274307-000  
D-436-0184



TE Part #405959-000  
22759/34-10-0



TE Part #218467-000  
22759/34-10-2

Documents

Product Drawings

S03-08-R

English

Datasheets & Catalog Pages

Raychem Electrical Interconnect Products

English

Product Specifications

Product Specification

English