

R10-E1Z4-115V ✓ ACTIVE

Potter & Brumfield | Potter & Brumfield R10


TE Internal #: 8-1393766-2

Potter & Brumfield R10, Power Relays, Industrial Panel Plug-In, Monostable, AC, 9000Ω Coil Resistance, Sensitive Version, 115VAC Coil Voltage Rating

[View on TE.com >](#)



Relays, Contactors & Switches > Relays > Power Relays



Power Relay Type: **Industrial Panel Plug-In**

Coil Magnetic System: **Monostable, AC**

Coil Resistance: **9000 Ω**

Coil Special Features: **Sensitive Version**

Coil Voltage Rating: **115 VAC**

Features

Product Type Features

Power Relay Type	Industrial Panel Plug-In
------------------	--------------------------

Electrical Characteristics

Insulation Initial Dielectric Between Coil & Contact Class	500 – 1000 V
Insulation Initial Dielectric Between Contacts & Coil	1000 Vrms
Actuating System	AC
Insulation Initial Dielectric Between Open Contacts	500 Vrms
Insulation Initial Dielectric Between Adjacent Contacts	1000 Vrms
Insulation Initial Resistance	10000 MΩ
Coil Magnetic System	Monostable, AC
Coil Resistance	9000 Ω
Coil Special Features	Sensitive Version
Coil Voltage Rating	115 VAC
Contact Switching Load (Min)	1mA @ 12V
Contact Voltage Rating	120 VAC

Body Features

Product Weight	40 g[1.41 oz]
----------------	---------------

Contact Features

Contact Special Features	Bifurcated/Twin Contacts
--------------------------	--------------------------



Contact Arrangement	4 Form C (CO)
Contact Current Class	0 – 2 A, 16 A
Contact Current Rating (Max)	2 A
Contact Material	Ag
Contact Number of Poles	4
Terminal Type	Plug-In, Solder

Mechanical Attachment

Relay Mounting Type	Socket
---------------------	--------

Dimensions

Length Class (Mechanical)	25 – 30 mm
Height Class (Mechanical)	30 – 40 mm
Width Class (Mechanical)	16 – 20 mm
Product Width	18.7 mm[.736 in]
Product Length	29.6 mm[1.165 in]
Product Height	30.2 mm[1.189 in]

Usage Conditions

Environmental Ambient Temperature Class	70 – 85 °C
Environmental Ambient Temperature (Max)	75 °C[167 °F]
Operating Temperature Range	-55 – 75 °C

Packaging Features

Packaging Method	Package
------------------	---------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2013 (144) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content



Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



TE Part # 1-1393143-2
27E129=SOCKET,R10,16,PC,PHEN



TE Part # 1393143-9
27E126=SOCKET,R10,16,SLG,PHE



TE Part # 1-1393143-5
27E152=SOCKET,R10,ASSY,W/BRK



TE Part # 2-1393143-2
27E194=SOCKET,R10,16,PC,PHEN



TE Part # 2-1393143-5
27E213=SOCKET,R10,16,PC,PHEN



TE Part # 4-1393143-4
27E461=SOCKETS



TE Part # 4-1393143-8
27E629=SOCKETS




TE Part # 5-1393143-1
27E637=SOCKETS




TE Part # 4-1393143-2
27E447=SOCKETS

Also in the Series | **Potter & Brumfield R10**



Board-to-Board Headers & Receptacles(1)



Power Relays(180)



Relay Accessories, Sockets & Clips(34)

Customers Also Bought




TE Part #1996220-2
RM3R88P106P106P-3301 (201)



TE Part #1-87270-0
4/05 LOCK CLIP HSG SR .156CL



TE Part #1-87270-2
05/06 LOCK CLIP HSG SR .156CL



TE Part #1-530785-1
BOX PIN 60 POS 075 C/L




TE Part #5-794682-2
22P MICRO MNL ASSY,VRT,THRU,L



TE Part #2-323199-1
DG 22-16COM 22-18MIL HR R6TAPE




TE Part #3-87962-9
80 MODII HORZ DR CE 100CL/115



TE Part #449810-1
PLUG ASSY WITH .25 POSTS,LGH



TE Part #ZPF000000000018226
FDDBA 50-16-21 SN-K



TE Part #2-1879683-8
H8 205R 0.1% 50PPM

Documents

[CAD Files](#)

[3D PDF](#)

[3D](#)

[Customer View Model](#)

[ENG_CVM_CVM_8-1393766-2_A.2d_dxf.zip](#)

[English](#)

[Customer View Model](#)

[ENG_CVM_CVM_8-1393766-2_A.3d_igs.zip](#)



English

Customer View Model

[ENG_CVM_CVM_8-1393766-2_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[R10 General Purpose Dry Circuit to 7.5 Amp Multicontact AC or DC Relay](#)

English

[Industrial Relays Quick Reference Guide](#)

English

[Industrial Relays Quick Reference Guide](#)

Japanese

[Industrial Relays Quick Reference Guide](#)

Product Specifications

[Definitions, Handling, Processing, Testing and Use of Relays](#)

English