




Wire Protection & Management > Heat Shrink Molded Shapes > Cable Transitions & Breakouts



Molded Part Shape: **Y Shape**
Number of Branches/Legs: **3**
Material Code: **4**
Breakout & Transition Material Systems Code: **10**
Adhesive Pre-Coat: **Yes**

Features

Product Type Features

Molded Part Shape	Y Shape
Size Code	034

Configuration Features

Number of Branches/Legs	3
-------------------------	---

Body Features

Material	Polyolefin Flexible Modified
Material Code	4
Breakout & Transition Material Systems Code	10
Adhesive Pre-Coat	Yes

Dimensions

Inside Diameter Range (Leg 2)	6.1 – 13.2 mm[.24 – .52 in]
Inside Diameter Range (Body)	13.7 – 26.9 mm[.54 – 1.06 in]
Inside Diameter Range (Leg 1)	13.7 – 26.9 mm[.54 – 1.06 in]

Usage Conditions

Operating Temperature Range	-55 – 135 °C[-67 – 275 °F]
-----------------------------	----------------------------

Operation/Application

Power Cable Accessory	No
-----------------------	----



Industry Standards

Government Qualified	No
----------------------	----

Other

Adhesive Code	86
Molded Part Shape Code	342A
Fluid/Chemical Resistance	Occasional exposure to fluids
Adhesive Options	/86 Precoat
Breakout & Transition Adhesive Type	High Performance Pre-Coat Adhesive

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # CJ2087-000
[HL2010E-KIT-120V](#)

Customers Also Bought



TE Part #984937-000
[362A014-4/86-0](#)



TE Part #823761-000
[322A158-4-0](#)



TE Part #154N-500A-R
[MEDIA ISOLATED PRESSURE STOCK LIST](#)



TE Part #YDTS24T09-98SCV001
[Jam Nut: D38999, 09-98 Insert LIST](#)



TE Part #D01425-000
[T1K WHITE POLYIMIDE LABELS](#)



TE Part #179911-000
[44B1111-22-9-9CS2275](#)




TE Part #927089-000
[44B1121-18-9/96-9CS2275](#)



TE Part #CZ4419-000
[55A1131-10-3/6/9-9](#)



TE Part #158551-000
[55A1141-18-MST4-9CS2275](#)



TE Part #265316-000
[81044/9-16-5](#)

Documents

Product Drawings

[342A034-4/86-0](#)

English

Datasheets & Catalog Pages

[1654025_Sec4_4](#)

English

[Raychem Molded Parts Visual Guide](#)

English



Product Specifications

Product Specification

English

Product Environmental Compliance

Safety Datasheet

Safety Datasheet

German

Safety Datasheet

German

Safety Datasheet

English

Safety Datasheet

English

Safety Datasheet

English

Safety Datasheet

Safety Datasheet

Safety Datasheet

French

Safety Datasheet

French

Safety Datasheet

Safety Datasheet

Safety Datasheet

Safety Datasheet

Safety Datasheet

Safety Datasheet

Safety Datasheet