

Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought







TE Part #1623722-4
Wirewound Resistor: Axial Mount, 17 Watt




TE Part #1625888-4
2W STD M/OX 5% 430R




TE Part #1-284511-6
16 POS TERMI-BLOK PLUG C. VITI




TE Part #1614353-9
RN 0603 2K67 0.1% 10PPM CUT LENGTH




TE Part #1614352-1
RN 0603 20K 0.1% 10PPM 5K RL




TE Part #1775284-3
AMP HPI 2.5MM HEADERS




TE Part #1108846-1
HC26.Base Housing-PCB



TE Part #2-1393203-8
V23148-A1007-A101



TE Part #1825013-6
MRD10CSTR04=7MM ROT DIP, BCD COMP



TE Part #644712-1
03P MTA156 HDR ASSY STR W/O#2

Documents

Product Drawings

.058 DIA PIN PC AUSNPB/NI/PHBZ

English

CAD Files

Customer View Model

ENG_CVM_60803-1_AJ1.3d_igs.zip

English

Customer View Model

ENG_CVM_60803-1_AJ1.3d_stp.zip

English

Customer View Model

ENG_CVM_60803-1_AJ1.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications



Application Specification

English

Product Environmental Compliance

TE Material Declaration

English