




Cable Assemblies > Data Bus Components > Data Bus Couplers



Coupler Type: **Box Coupler**
Number of Stubs: **3**
Coupler Style: **Bayonet**
Eyelet: **Without**
Polarization (Bayonet Style): **A**

Features

Product Type Features

Product Type	Data Bus Component
Coupler Type	Box Coupler

Configuration Features

Arrangement	Face
Number of Stubs	3
Eyelet	Without

Termination Features

Connection Type	Solder
-----------------	--------

Mechanical Attachment

Coupler Style	Bayonet
Polarization (Bayonet Style)	A

Usage Conditions

Operating Temperature (Max)	125 °C
-----------------------------	--------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant




China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUL 2019 (201) SVHC > Threshold: Pb (37% in Solder) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 019439-000
DK-621-0433-1P


Customers Also Bought




TE Part #434377-000
HEX40-AB-00-13-A3-2



TE Part #1589687-4
QCM019SC2DM052PB = Circular



TE Part #601101-000
D-602-0104




TE Part #387811-000
44A1111-20-4-9




TE Part #3318953001
[44A1161-22-0/1/2/3/4/5-9](#)




TE Part #E146163001
[55A9012-30-4/5](#)



TE Part #280529-000
[D-500-0255-545-1](#)



TE Part #393937-000
[D-621-0457-L](#)



TE Part #4-1589777-3
[STM065SC2DM024N = WDUALOBE](#)



TE Part #1775635-6
[0.5mm FPC Connectors](#)

Documents

Product Drawings

[D-500-0255-533-1](#)

English

Datasheets & Catalog Pages

[Data Bus Components Brochure](#)

English

Product Specifications

[Specification Or Standard](#)

English