



Wire Protection & Management > Heat Shrink Molded Shapes > Heat Shrink Boots > Heat Shrink Boots: Non Lipped, Right Angle



Molded Part Shape: 90°

Molded Part Shape Code: 222A

Lipped: No

Material Code: 3

Heat Shrink Boot Material Systems Code: 10

[All Heat Shrink Boots: Non Lipped, Right Angle \(136\)](#)

Features

Product Type Features

|                   |     |
|-------------------|-----|
| Molded Part Shape | 90° |
|-------------------|-----|

Configuration Features

|        |    |
|--------|----|
| Lipped | No |
|--------|----|

Body Features

|                                        |                                |
|----------------------------------------|--------------------------------|
| Material Code                          | 3                              |
| Heat Shrink Boot Material Systems Code | 10                             |
| Adhesive Pre-Coat                      | No                             |
| Material                               | Semi-Rigid Modified Polyolefin |

Usage Conditions

|                             |                            |
|-----------------------------|----------------------------|
| Operating Temperature Range | -55 – 135 °C[-67 – 275 °F] |
|-----------------------------|----------------------------|

Other

|                           |                               |
|---------------------------|-------------------------------|
| Molded Part Shape Code    | 222A                          |
| Fluid/Chemical Resistance | Occasional exposure to fluids |
| Adhesive Type             | Adhesive Purchased Separately |

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)



|                                               |                                                                                                                               |
|-----------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                     |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                     |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                       |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2021 (211)<br>Candidate List Declared Against: JAN 2021 (211)<br>Does not contain REACH SVHC |
| Halogen Content                               | Not Low Halogen - contains Br or Cl > 900 ppm.                                                                                |
| Solder Process Capability                     | Not applicable for solder process capability                                                                                  |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # CJ2087-000  
HL2010E-KIT-120V


Customers Also Bought




TE Part #1057780-1  
3152 1201 10,TNC FLANGE JACK



TE Part #180924  
FF 250 TAB HSG 2P NYLON NAT



TE Part #180923  
FF 250 REC HSG 2P NYLON NAT



TE Part #2-1879747-6  
RP 1J 115K 0.1% 15PPM CUT LENGTH



TE Part #YDTS26W21-39PNV001  
D38999: Straight Plug, 21-39 Insert



TE Part #1337772-4  
50/OHM COAX BNC STR PLUG ELB P




TE Part #1649329-2  
RTE24006



TE Part #2180043002  
55A0811-22-2



TE Part #2180053002  
55A0811-22-6



TE Part #1522117-1  
15-1048-3=CAP NUT

Documents

Datasheets & Catalog Pages

Raychem Molded Parts Visual Guide

English

Product Specifications

Product Specification

English

Product Environmental Compliance

Safety Datasheet

Safety Datasheet

German

Safety Datasheet

English

Safety Datasheet

Safety Datasheet

French

Safety Datasheet

Safety Datasheet

Safety Datasheet

Safety Datasheet