

SSRK-600D30

✓ ACTIVE

Potter & Brumfield | Potter & Brumfield SSRK

TE Internal #: 6-1393030-8

Potter & Brumfield SSRK, Power Relays, Solid State, Contact
Arrangement 1 Form A (SPST-NO), DIN Rail Relay Mounting Type

[View on TE.com >](#)



Relays, Contactors & Switches > Relays > Power Relays > P&B SSRK SERIES SOLID STATE RELAYS



Power Relay Type: **Solid State**
Contact Arrangement: **1 Form A (SPST-NO)**
Relay Mounting Type: **DIN Rail**

[All P&B SSRK Series Solid State Relays \(12\)](#)

Features

Product Type Features

Output Type	AC
Power Relay Type	Solid State

Configuration Features

Output Switching	Zero
------------------	------

Electrical Characteristics

Input Voltage Typical	4 VDC
Output Voltage (Max)	660 V
Output Voltage Rating (AC Relays)	48 – 660 Vrms
Output Current Rating	.15 – 30 Arms
Output Voltage Rating (DC Relays)	48 – 660 VDC
Output Current (Min)	.15 A
Insulation Initial Dielectric Between Contacts & Coil	4000 Vrms

Body Features

Product Weight	280 g[9.87 oz]
----------------	----------------



Case Color	Black
Contact Features	
Switch Arrangement	1 Form A (SPST-NO)
Contact Arrangement	1 Form A (SPST-NO)
Termination Features	
Relay Termination Type	Finger-Safe (IP20) Screw Clamps
Mechanical Attachment	
Coupling	Optical
Relay Mounting Type	DIN Rail
Housing Features	
Relay Housing Style	DIN Mount with Integral Heatsink
Dimensions	
Dimensions (L x W x H) (Approximate)	82.3 x 22.5 x 111.5 mm[3.24 x .886 x 4.39 in]
Usage Conditions	
Operating Temperature Range	-30 – 80 °C
Operation/Application	
R-Switch & slimSSR Relays	Yes

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (3.5% in Component) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # CAT-P851-SS61F
P&B SSRM SERIES SOLID STATE RELAYS

Also in the Series | Potter & Brumfield SSRK

Power Relays(12)

Customers Also Bought


TE Part #1-6450869-4
V/R 2ACP+1LP+32S+3HDP+1LP+1P

TE Part #1410188-3
MULTIGIG RT T2 7RW DC DF F-RGT

TE Part #1-1469492-1
MULTIGIG RT 9MM GUIDE/ESD 0 DEG

TE Part #104257-7
08 MTE RCPT HSG SR LATCH .100






TE Part #104480-4
SHORT POINT CONT 30 DPLX STMPD




TE Part #1-84953-1
1MM FPC HORZ.TOP CONT.ASSY 11P



TE Part #104480-8
SHORT POINT RCP CONT LP



TE Part #YDTS24W11-35PEV001
Jam Nut: D38999, 11-35 Insert



TE Part #1-104480-5
SHORT POINT RCP CONT LP



TE Part #1-1437601-9
PICOD301AK=PICO-D-301-AK-2

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_6-1393030-8_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_6-1393030-8_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_6-1393030-8_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Solid State Relay SSRK Series Data Sheet

English

Potter & Brumfield SSRK SSRM Series

English

Industrial Relays Quick Reference Guide

English

Industrial Relays Quick Reference Guide

Japanese

Industrial Relays Quick Reference Guide