




Wire Protection & Management > Heat Shrink Molded Shapes > Heat Shrink Boots > Heat Shrink Boots: Non Lipped, Straight



Molded Part Shape: 180°

Molded Part Shape Code: 202

Lipped: No

Material Code: 3

Heat Shrink Boot Material Systems Code: 10

[All Heat Shrink Boots: Non Lipped, Straight \(171\)](#)

Features

Product Type Features

|                   |      |
|-------------------|------|
| Molded Part Shape | 180° |
|-------------------|------|

Configuration Features

|        |    |
|--------|----|
| Lipped | No |
|--------|----|

Body Features

|                                        |                                |
|----------------------------------------|--------------------------------|
| Material Code                          | 3                              |
| Heat Shrink Boot Material Systems Code | 10                             |
| Adhesive Pre-Coat                      | No                             |
| Material                               | Semi-Rigid Modified Polyolefin |

Dimensions

|                             |                 |
|-----------------------------|-----------------|
| Inside Diameter as Supplied | 24.6 mm[.97 in] |
|-----------------------------|-----------------|

Usage Conditions

|                             |                            |
|-----------------------------|----------------------------|
| Operating Temperature Range | -55 – 135 °C[-67 – 275 °F] |
|-----------------------------|----------------------------|

Operation/Application

|                       |    |
|-----------------------|----|
| Power Cable Accessory | No |
|-----------------------|----|

Industry Standards

|                    |                      |
|--------------------|----------------------|
| Approved Standards | SAE AS81765/1 Type I |
|--------------------|----------------------|



Government Qualified

No

Other

|                           |                               |
|---------------------------|-------------------------------|
| Molded Part Shape Code    | 202                           |
| Fluid/Chemical Resistance | Occasional exposure to fluids |
| Adhesive Options          | /42 Precoat                   |
| Adhesive Type             | Adhesive Purchased Separately |

Product Compliance

For compliance documentation, visit the product page on TE.com>


|                                               |                                                                                                                               |
|-----------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                     |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                     |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                       |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2021 (211)<br>Candidate List Declared Against: JAN 2021 (211)<br>Does not contain REACH SVHC |
| Halogen Content                               | Not Low Halogen - contains Br or Cl > 900 ppm.                                                                                |
| Solder Process Capability                     | Not applicable for solder process capability                                                                                  |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts






TE Part # 890060-000  
[S1017-1.0X50](#)



TE Part # CJ2087-000  
[HL2010E-KIT-120V](#)

Customers Also Bought



TE Part #170366-1  
[MINI UNIVERSAL M-N-L SOCKET LP](#)




TE Part #172233-1  
[2 POS MINI UMNL CAP HOUSING](#)



TE Part #1841-1-5620  
[CONT PIN](#)




TE Part #046377-000  
[Heat Shrink Boots: Non Lipped, Right Angle](#)



TE Part #042045-000  
[Bulbous Heat Shrink Boots: Lipped, Straight](#)



TE Part #1-1617146-2  
[JMGACD-26M = M39016/18-036M](#)



TE Part #210783-000  
[562A067-25/225-0](#)



TE Part #YDTS24W21-11SAV001  
[Jam Nut: D38999, 21-11 Insert](#)



TE Part #1616095-5  
[NN449B \(FAA/PMA\)=RELAY](#)



TE Part #1841-1-5612  
[CONT PIN](#)

Documents

Product Drawings

[202A121-3-00-0](#)

English

Datasheets & Catalog Pages

[1654025\\_Sec4\\_-3](#)

English

[Raychem Molded Parts Visual Guide](#)

English



---

**Product Specifications**

[Product Specification](#)

English

---

**Product Environmental Compliance**

[Safety Datasheet](#)

[Safety Datasheet](#)

German

[Safety Datasheet](#)

English

[Safety Datasheet](#)

[Safety Datasheet](#)

French

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)