

KUMP-11A18-24

✓ ACTIVE

Potter & Brumfield | Potter & Brumfield KUMP

TE Internal #: 6-1393116-3

Potter & Brumfield KUMP, Power Relays, Industrial Panel Plug-In,
Monostable, AC, 2 – 3VA Coil Power Rating Class, 2.8VA Coil
Power Rating AC

[View on TE.com >](#)



Relays, Contactors & Switches > Relays > Power Relays



Power Relay Type: **Industrial Panel Plug-In**
Coil Magnetic System: **Monostable, AC**
Coil Power Rating Class: **[2 – 3 VA]**
Coil Power Rating AC: **2.8 VA**
Coil Resistance: **72 Ω**

Features

Product Type Features

Power Relay Type	Industrial Panel Plug-In
------------------	--------------------------

Electrical Characteristics

Insulation Initial Dielectric Between Coil & Contact Class	1500 – 2500 V
Insulation Initial Dielectric Between Contacts & Coil	2200 Vrms
Actuating System	AC
Insulation Initial Dielectric Between Open Contacts	1200 Vrms
Contact Limiting Making Current	15 A
Contact Limiting Short-Time Current	15 A
Contact Limiting Continuous Current	15 A
Insulation Initial Dielectric Between Adjacent Contacts	2200 Vrms
Insulation Initial Resistance	100 MΩ
Contact Limiting Breaking Current	15 A
Coil Magnetic System	Monostable, AC
	2 – 3 VA
Coil Power Rating AC	2.8 VA
Coil Resistance	72 Ω
Coil Special Features	UL Coil Insulation Class B
Coil Voltage Rating	24 VAC



Contact Switching Load (Min)	300mA @ 12V
Contact Voltage Rating	277 VAC

Body Features

Product Weight	85 g[2.988 oz]
----------------	----------------

Contact Features

Contact Arrangement	2 Form C (CO)
Contact Current Class	10 – 20 A, 16 A
Contact Current Rating (Max)	15 A
Contact Material	AgCdO
Contact Number of Poles	2
Terminal Type	Quick Connect, Solder

Mechanical Attachment

Relay Mounting Type	Socket
---------------------	--------

Dimensions

Length Class (Mechanical)	35 – 40 mm
Height Class (Mechanical)	40 – 50 mm
Width Class (Mechanical)	30 – 40 mm
Product Width	35.7 mm[1.405 in]
Product Length	38.9 mm[1.55 in]
Product Height	50 mm[1.97 in]

Usage Conditions

Environmental Ambient Temperature Class	50 – 70 °C
Environmental Ambient Temperature (Max)	55 °C[131 °F]
Operating Temperature Range	-45 – 55 °C

Packaging Features

Packaging Method	Package
------------------	---------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JAN 2021 (211)
Candidate List Declared Against: JAN 2021 (211)
SVHC > Threshold:
Cadmium oxide (5.1% in Component Part)
Article Safe Usage Statements:
Use personal protective equipment as required. Do not eat, drink or smoke when using this product. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen ContentNot Yet Reviewed for halogen content

Solder Process CapabilityNot applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 2-1419106-5
27E893=SOCKET,KU,11,QC,POLY,NA-

TE Part # 1419106-4
27E046=SOCKET,KU,11,PC,NYL,NAT

TE Part # 1393143-1
27E043=SOCKET,KU,11,SLG,NYL,N


TE Part # 1393143-5
27E121=SOCKET,KUP,11,SCW,PLE

TE Part # 3-1393143-8
27E396=SOCKETS

TE Part # 6-1393116-8
KUMP-11A58-24=KU

TE Part # 1393143-2
27E067=SOCKET,KU,11,QC.187,NY

Also in the Series | Potter & Brumfield KUMP



Power Relays(32)

Customers Also Bought



TE Part #1-1734260-5
AMP HPI 1.25MM HEADERS




TE Part #1-213825-7
CPC SERIES 1 POSTED



TE Part #1-2308107-0
DDR4 DIMM SOCKETS




TE Part #1419111-3
20C228=SPRING,HOLD-DOWN,KUP,.0



TE Part #1-440146-5
1.25mm WTB Socket,Housing,15p



TE Part #1393139-7
MDR-135-1=MDR



TE Part #1520117-1
8910K94=10 AMP TOGGLE



TE Part #9-2176311-3
RP 1E 0.1W 10K5 0.1% 25PPM 1K RL



TE Part #1438136-1
GET .64 CONNECTOR SYSTEM,
CONNECTOR HSG



TE Part #1-2273012-3
M8 R/A LED PIGTAIL

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_6-1393116-3_D_c-6-1393116-3-d.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_6-1393116-3_D_c-6-1393116-3-d.3d_igs.zip



English

Customer View Model

[ENG_CVM_CVM_6-1393116-3_D_c-6-1393116-3-d.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[KUM-KUMP Series Relay Datasheet](#)

English

[Industrial Relays Quick Reference Guide](#)

English

[Industrial Relays Quick Reference Guide](#)

Japanese

[Industrial Relays Quick Reference Guide](#)

Product Specifications

[Definitions, Handling, Processing, Testing and Use of Relays](#)

English