



Identification & Labeling > Printable Tubing



Printable Tubing Type: **Ladder**

Printable Tubing Grade: **Fluid Resistant**

Printable Tubing Shrink Ratio: **3:1**

Primary Product Color: **Yellow**

Markers per Sleeve: **1**

Features

Product Type Features

Printable Tubing Type	Ladder
Printable Tubing Grade	Fluid Resistant

Body Features

Printable Tubing Shrink Ratio	3:1
Primary Product Color	Yellow
Markers per Sleeve	1

Dimensions

Product Length	12.7 mm[.5 in]
Supplied Inner Diameter	4.75 mm[.187 in]
Recovered Inside Diameter	1.57 mm[.062 in]
Compatible Cable Diameter Range	6.9 – 1.62 mm[.275 – .64 in]

Usage Conditions

Operating Temperature Range	-75 – 135 °C[-103 – 275 °F]
-----------------------------	-----------------------------

Operation/Application

Recommended Ribbon	See TE Document 411-121005 the Printer Product Ribbon Matrix
--------------------	--

Printer/Label Features

Recommended Printer	See TE Document 411-121005 the Printer Product Ribbon Matrix
Printer Technology	Thermal Transfer



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Part # 1-2186500-1
T3212-PRINTER




TE Part # 1-2186502-1
T3224-PRINTER




TE Part # 1-2186503-1
T3224-SWARE-PRINTER



TE Part # CP8122-000
T6112DS-PRINTER




TE Part # 311292-000
TMS-RJS-RIBBON-4DSCE




TE Part # F55931-000
1966-RIBBON



TE Part # 1-2186501-1
T3212-SWARE-PRINTER



TE Part # 1-2186538-1
RIB-1982-300-110-L-0



TE Part # 1-2186540-1
RIB-1982-300-60-L-0



TE Part # 1-2186549-1
RIB-1982-240-110-L-0-T200

Customers Also Bought



TE Part #1-2823449-4
M12 STRAIGHT CRIMPED STRAIN RELIEF



TE Part #147547-000
D-SCE FLUID RESISTANT SLEEVES



TE Part #042313-000
B-150-23




TE Part #2160053004
55A0111-20-9




TE Part #2160403001
55A0111-22-1



TE Part #176819-000
B-150-11



TE Part #1824133001
55K9082-24-2/6



TE Part #2820023007
44A0111-16-2



TE Part #F759273001
FLHTC0311-18-45



TE Part #0908913002
FLHTC0311-22-6

Documents



Product Drawings

D-SCE-18-50-4

English

Product Specifications

Product Specification

English

Instruction Sheets

Instruction Sheet (non U.S.)

English