




AMP

TE Internal #: 90546-2
Portable Crimp Tools, Commercial Crimp Tooling, Operator
Releasable & Adjustable, Removable/Interchangeable, TE Product
Specification (114-)
[View on TE.com >](#)

Application Tooling > Portable Crimp Tools



Tool Grade: **Commercial Crimp Tooling**
Ratchet Configuration: **Operator Releasable & Adjustable**
Die Sets Type: **Removable/Interchangeable**
Specification Type: **TE Product Specification (114-)**
TE Certification: **Upon Request for Fee**

Features

Other

Crimp Form-Wire Barrel Type	Open Barrel - F Crimp
Tool Grade	Commercial Crimp Tooling
Ratchet Configuration	Operator Releasable & Adjustable
Die Sets Type	Removable/Interchangeable
Specification Type	TE Product Specification (114-)
TE Certification	Upon Request for Fee
Power Technology Type	Battery, Electric, Manual
Tooling Type	Standard Die Envelope (SDE) Die Set

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per



homogenous material. Also BFR/CFR/PVC Free











Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

 TE Part # 2280380-1 KIT, BT, MICRO SDE, 110V	 TE Part # 1-770251-0 UMNLI SOK PTPPHBZ LP LF 20-14	 TE Part # 350550-7 UMNLI SOK 20-14 AU/BR L/P	 TE Part # 350547-7 UMNLI PIN 20-14 AUBR L/P
 TE Part # 1-770250-0 UMNLI PIN SN/AUNI/BR LP20-14	 TE Part # 770250-1 UMNLI PIN PTPBR LP 20-14	 TE Part # 350550-6 UMNLI SOK 20-14 AU/PHBZ L/P	 TE Part # 350705-7 UMNLI SPLIT PIN 20-14 AUBR L/P
 TE Part # 350547-3 UMNLI PIN 20-14 PTPPHBZ L/P	 TE Part # 350547-2 UMNLI PIN 20-14 AUBR L/P	 TE Part # 350547-6 UMNLI PIN 20-14 AU/PHBZ L/P	 TE Part # 350669-1 UMNLI GRND PIN 20-14 PTPBR L/P



			
TE Part # 350547-1 UMNL PIN 20-14 PTPBR L/P	TE Part # 350705-1 UMNL SPLIT PIN 20-14 PTPBR L/P	TE Part # 350218-6 UMNL PIN 20-14 .0125AUPHBZ	TE Part # 350687-7 UMNL SPLIT PIN AUNI/BR
			
TE Part # 770210-1 UMNL GRND PIN PTPBR	TE Part # 350218-7 UMNL PIN 20-14 .0126AUBR	TE Part # 350654-1 UMNL GRND PIN 20-14 PTPBR	TE Part # 350687-2 UMNL SPLIT PIN AUBR

Customers Also Bought

			
TE Part #1804030-1 EXTRACTION TOOL ASSY	TE Part #189727-1 EXTRACTION TOOL	TE Part #350551-3 UMNL SOK 20-14 PTPPHBZ L/P	TE Part #1879216-6 CPF 0402 56K2 0.1% 25PPM 1K RL
			
TE Part #170366-4 MINI UNIVERSAL M-N-L SOCKET LP	TE Part #F61662-000 HW HIGH TACK WHITE POLYESTER LABELS	TE Part #1604256-1 UMNL BULKHEAD CONN,4 POS	TE Part #1241375-1 AMP MCP 1.5K, CONTACT, (LP)
			
TE Part #2-1904020-4 V23234A0001X037-EV-100	TE Part #1SNS320001Z3777 HD 6/14.SDH3 with DIODE DSA9-16F		

Documents



Datasheets & Catalog Pages

1-1773865-2_1015_Commercial Manual Hand Tools

English

Crimp Term Whitepaper-Use the Right Tool 1-1773953-1

English

Bottoming Dies

English

CRIMPING WHERE FORM MEETS FUNCTION

English

Instruction Sheets

Instruction Sheet (U.S.)

English

PRO-CRIMPER II Hand Tool Assembly 90546-1 w/Die Assembly 90546-2

English

Instruction Sheet (U.S.)

English