



Application Tooling > Portable Crimp Tools



Tool Grade: **Commercial Crimp Tooling**
Ratchet Configuration: **Operator Releasable & Adjustable**
Die Sets Type: **Removable/Interchangeable**
Specification Type: **TE Product Specification (114-)**
TE Certification: **Upon Request for Fee**

Features

Other

Crimp Form-Wire Barrel Type	Open Barrel - F Crimp
Tool Grade	Commercial Crimp Tooling
Ratchet Configuration	Operator Releasable & Adjustable
Die Sets Type	Removable/Interchangeable
Specification Type	TE Product Specification (114-)
TE Certification	Upon Request for Fee
Power Technology Type	Battery, Electric, Manual
Tooling Type	PRO-CRIMPER Hand Tool

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2019 (197) SVHC > Threshold: Not Yet Reviewed




Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.


Compatible Parts




TE Part # 171638-1
MINI U-M-N-L PIN CONT. L.P




TE Part # 171639-1
MINI U-M-N-L SOCKET L.P



TE Part # 171636-1
MINI U-M-N-L PIN CONTACT













TE Part # 171637-1
MINI U-M-N-L SOCKET CONTACT



TE Part # 171637-2
MINI U-M-N-L SOCKET CONT AS

Customers Also Bought



 <p>TE Part #206137-2 CPC SERIES 3</p>	 <p>TE Part #91521-1 CCII TYPE III+ PIN SKT 18-14 ASSY</p>	 <p>TE Part #189727-1 EXTRACTION TOOL</p>	 <p>TE Part #2063388-1 TOOL, EXTRACTION</p>
 <p>TE Part #4-1879214-1 CPF 0402 866R 0.1% 25PPM 1K RL</p>	 <p>TE Part #171638-1 MINI U-M-N-L PIN CONT. L.P</p>	 <p>TE Part #171639-1 MINI U-M-N-L SOCKET L.P</p>	 <p>TE Part #2178186-4 ELCON MINI 2P CABLE CONN,6MM2, W/O CODING</p>
 <p>TE Part #455830-1 INSERTION TOOL</p>	 <p>TE Part #1-1478204-0 BNC Str PCB Skt 50Ohm Silver P</p>		

Documents

Datasheets & Catalog Pages

1-1773865-2_1015_Commercial Manual Hand Tools

English

Crimp Term Whitepaper-Use the Right Tool 1-1773953-1

English

Bottoming Dies

English

CRIMPING WHERE FORM MEETS FUNCTION

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)

English

PRO-CRIMPER II Hand Tool Assembly 90760-1 w/Die Assembly 90760-2

English

