820-AG11D × OBSOLETE

DIPLOMATE 800 Series

TE Internal #: 6-1437537-6 TE Internal Description: 820-AG11D=SOCKET ASSY DIP Socket: Standard, Screw Machine, Open, Gold

View on TE.com >



All DIP Socket: Standard, Screw Machine, Open, Gold (1)

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU

EU ELV Directive 2000/53/EC

China RoHS 2 Directive MIIT Order No 32, 2016

EU REACH Regulation (EC) No. 1907/2006

Not Compliant

Not Compliant

Restricted Materials Above Threshold

Current ECHA Candidate List: JAN 2021

(211)

Candidate List Declared Against: JAN 2021

(211)

SVHC > Threshold:

Pb (13% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after



handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Solder Process Capability

Not Low Halogen - contains Br or Cl > 900 ppm.

Wave solder capable to 265°C


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach


Also in the Series DIPLOMATE 800 Series

820-AG11D=SOCKET ASSY





Customers Also Bought



10 POWER TAP ASSY WITH SCREW #6-32



TE Part #1-1571983-3 GDH10S04=DIP SWITCH

Documents

Product Drawings 820-AG11D=SOCKET ASSY

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_6-1437537-6_E.2d_dxf.zip

C For support call+1 800 522 6752

820-AG11D



English

Customer View Model ENG_CVM_CVM_6-1437537-6_E.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_6-1437537-6_E.3d_stp.zip

English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use.

Datasheets & Catalog Pages DIP Sockets Quick Reference Guide (EN)

English

Product Environmental Compliance Product Compliance English

Product Compliance

English