



Relays, Contactors & Switches > Switches > Toggle Switches



Configuration (Pole-Throw): **Single Pole - Double Throw**

Bushing Thread Size: **1/4-40**

Sealed Toggle Switch: **Yes**

Contact Base Material: **Copper Alloy**

Switch Contact Plating Material: **Gold Flash over Silver**

## Features

### Product Type Features

Product Type	Switch
Sealed Toggle Switch	Yes
Toggle Style	Baton Long
Toggle Switch Type	Toggle
Toggle Actuation	Vertical

### Configuration Features

Configuration (Pole-Throw)	Single Pole - Double Throw
Operating Function	On Off On

### Electrical Characteristics

Dielectric Strength	1500 VAC
UL/CSA Current Rating (125V)	3 A
Insulation Resistance	1000 MΩ
UL/CSA Current Rating (250V)	3 A
Contact Resistance	10 mΩ
Toggle Switch Voltage Rating	125 VAC

### Body Features

Actuator Finish	Chrome
Color	Green



Bushing Thread Size	1/4-40
Toggle Switch Seal Type	Internal Actuator O-Ring, Terminal Seal (Insert Molded)
Bushing Style	Threaded

#### Contact Features

Contact Base Material	Copper Alloy
Switch Contact Plating Material	Gold Flash over Silver
Toggle Switch Contact Current Rating	6 A

#### Termination Features

Termination Type	Vertical, Wire Lugs
------------------	---------------------

#### Mechanical Attachment

Toggle Switch Mounting Type	Panel
-----------------------------	-------

#### Housing Features

Process Sealed	Yes
----------------	-----

#### Dimensions

Toggle Length	10.49 mm [.413 in]
---------------	--------------------

#### Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

#### Other

Comment	UL available when ordering - consult factory.
---------	---

#### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (3.7% in component) 1,6,7,8,9,14,15,16,17,17,18,18-dodecachloropentacyclo



[12.2.1.16,9.02,13.05,10]octadeca-7,15-diene (Dechlorane Plus) (6.7% in component)

**Article Safe Usage Statements:**

Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Do not handle until all safety precautions have been read and understood. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Wave solder capable to 265°C

**Product Compliance Disclaimer**

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # 6-1437558-8  
MTE106D=(MSTE) SW TOG WATERPRO



TE Part # 7-1437558-2  
MTE206N=(MSTE) SWITCH TOGGLE W



TE Part # 7-1437558-3  
MTE206P=(MSTE) SW TOG WATERPRO



TE Part # 7-1437558-8  
MTE306D=(MSTE) SW TOG WATERPRO



TE Part # 7-1437558-1  
MTE106G=(MSTE) SW TOG WATERPRO



TE Part # 7-1437558-5  
MTE206R=(MSTE) SW TOG WATERPRO

Also in the Series | **Alcoswitch MTE**




Insertion &amp; Extraction Tools(1)



Toggle Switches(7)

## Customers Also Bought

TE Part #1-1437558-1  
MTA106DPC=(MSTA) SW TOG P/C TETE Part #2-1437558-2  
MTA206P=(MSTA) SW TOG DPDTTE Part #2-640454-4  
Polyester Vertical PCB Header: 2.54 mm, With Mating Alignment, UnshroudedTE Part #165026  
SOLIS 12-10 R M6TE Part #2-748003-0  
D-Sub Plug Assembly: Standard, Vertical, Shell Size 1, 2.74mmTE Part #1927574004  
Dual Wall Heat Shrink Tubing: SpoolTE Part #1600606-2  
PANEL MT RECPT HSG W/GUIDES PTE Part #1-103644-9  
20 MTE RCPT SR LATCH .100CLTE Part #ZPF000000000101093  
FDDBA 50-12-10 SN-K 090 A1386TE Part #105679-000  
55A6253-20-9/96-9CS2275

## Documents

### Product Drawings

MTE106E=(MSTE) SW TOG WATERPRO

English

### CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_6-1437558-9\_D.2d\_dxf.zip



English

**Customer View Model**

[ENG\\_CVM\\_CVM\\_6-1437558-9\\_D.3d\\_igs.zip](#)

English

**Customer View Model**

[ENG\\_CVM\\_CVM\\_6-1437558-9\\_D.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

**Datasheets & Catalog Pages**

[2-1773458-6\\_GREEN\\_SERIES\\_SWITCHES](#)

English