



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts

TE Part # 1393143-6
27E122=SOCKET,KRP,8,SCW,PLES

TE Part # 2-1419106-3
27E891=SOCKET,KRPA,8,OCTAL,POL



Also in the Series | [Potter & Brumfield KRPA](#)



[Power Relays\(60\)](#)




[Relay Accessories, Sockets & Clips\(5\)](#)


Customers Also Bought




TE Part #1558662-9
[PCB Power Relay: 30 amp, Monostable DC](#)




TE Part #8-2176403-5
[3550 3K3 1%](#)



TE Part #1757312-1
[RME2R106S22Q2P-0101 \(201\)](#)



TE Part #1757313-1
[RME2P106P22Q2S-4601 \(201\)](#)




TE Part #1757313-2
[RME2P106P22Q2S-4602 \(201\)](#)



TE Part #1484576-1
[2001-5544-02 SMA CABLE PLUG](#)




TE Part #1-2373378-2
[12P,2MM,SHRD HDR,DRV,T,SMD,0.76 AU,TB](#)



TE Part #1045383-1
[SCD,2001 7316 00,SMA](#)



TE Part #1329533-1
[SCD,3752 5037 02,TNC](#)



TE Part #1589954-1
[QCM019M5P = Circular](#)

Documents

[CAD Files](#)

[3D PDF](#)

[3D](#)

[Customer View Model](#)

[ENG_CVM_CVM_9-1393101-4_D.2d_dxf.zip](#)

[English](#)

[Customer View Model](#)



[ENG_CVM_CVM_9-1393101-4_D.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_9-1393101-4_D.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[KRPA, KRP, KA, KR 5 to 10 Amp General Purpose Relay](#)

English

Industrial Relays Quick Reference Guide

English

Industrial Relays Quick Reference Guide

Japanese

Industrial Relays Quick Reference Guide

Product Specifications

Definitions, Handling, Processing, Testing and Use of Relays

English