



CII

TE Internal #: 6-1617815-0

Time Delay Relays, Fixed, 28VDC Time Delay Relay Input Voltage, 10A@28VDCA / 115VACA Time Delay Relay Contact Current Rating, Delay on Release

[View on TE.com >](#)

Relays, Contactors & Switches > Relays > Time Delay Relays



Type of Control: **Fixed**

Time Delay Relay Input Voltage: **28 VDC**

Time Delay Relay Contact Current Rating: **10A@28VDC A, 115VAC A**

Mode of Operation: **Delay on Release**

Delay Time: **.1 seconds**

Features

Product Type Features

Enclosure Type	Hermetic Sealed Metallic
Product Type	Relay
Relay Type	Time Delay
Product Category	Electromechanical Relays
Magnetic Blow-Out Device	Without

Configuration Features

Status Indicator Type	None
Multiple Timing Ranges	Without

Electrical Characteristics

Actuating System	DC
Time Delay Relay Input Voltage	28 VDC

Contact Features

Contact Arrangement	2 Form C, DPDT, 2 C/O
Contact Base Material	Silver Cadmium Oxide
Type of Control	Fixed
Time Delay Relay Contact Current Rating	10A@28VDC A, 115VAC A
Delay Time	.1 seconds



Termination Features

Termination Type	Solder Pin Terminal
------------------	---------------------

Dimensions

Dimensions (L x W x H) (Approximate)	25.79 x 25.79 x 25.4 mm[1.015 x 1.015 x 1 in]
--------------------------------------	---

Usage Conditions

Operating Temperature Range	-55 – 125 °C
-----------------------------	--------------

Operation/Application

Mode of Operation	Delay on Release
-------------------	------------------

Other

Repeatability (Max)	±10%
---------------------	------

Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.




Compatible Parts




TE Part # 2-1617749-5
FCA-210-1027M=M83536/10-027M


Customers Also Bought




TE Part #342117-1
22-16 F.E.P.G. SPADE 4BA STUD




TE Part #9-2176397-8
3502 11K 1%




TE Part #2176398-2
3502 15K 1%




TE Part #EC1253-000
Z-TYPE PUSH-ON MARKERS




TE Part #342066
16-14 H.D.R/T 1/2" STUD BLACK




TE Part #165565-6
110 PIDG FASTON REC




TE Part #1755170-1
7022OCIM=RLY,STD,OFF,2P,24V,15S,I, M



TE Part #7-1472995-0
7012WDS=RLY,STD,ON,2P,96V,50S,S



TE Part #6-1755142-4
7022WDIM=RLY,STD,OFF,2P,96V,50S,I, M



TE Part #EC0437-000
06153411

Documents

- CAD Files
- 3D PDF
- 3D
- Customer View Model
- ENG_CVM_CVM_6-1617815-0_A.2d_dxf.zip
- English
- Customer View Model



[ENG_CVM_CVM_6-1617815-0_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_6-1617815-0_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[High_Performance_Relays_Section5](#)

English