

828-AG11D-ES

☒ SUPERSEDED


DIPLOMATE 800 Series

TE Internal #: 9-1437539-1

TE Internal Description: 828-AG11D-ES=SOCKET ASSY

DIP Socket: Standard, Stamped & Formed, Open, Gold

[View on TE.com >](#)



All DIP Socket: Standard, Stamped & Formed, Open, Gold (4)

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)


EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (13% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Also in the Series | DIPLOMATE 800 Series



DIP Sockets(5)

Customers Also Bought




TE Part #103673-5
06 MTE HDR SRRA LATCH W/HLDWN



TE Part #1-534237-4
16 MODII VRT SR CE 100/115



TE Part #103309-5
020 LOPRO HDR SP 30DP




TE Part #104128-5
026 LOPRO HDR SP 30DP LATCH



TE Part #104068-1
20 SYSTEM 50 HDR DRST SHRD



TE Part #103673-2
03 MTE HDR SRRA LATCH W/HLDWN



TE Part #103670-4
05 MTE HDR SRST LATCH W/HLDWN



TE Part #103904-9
10 MTE HDR SRRA LATCH W/HLDWN



TE Part #1-1437540-6
840-AG11D-ES=SOCKET ASSY

TE Part #GC1074U-3-0
NTC THERMISTOR, GLASS ENCAPSUL

Documents

Product Drawings

828-AG11D-ES=SOCKET ASSY

English

CAD Files



3D PDF

3D

Customer View Model

[ENG_CVM_CVM_9-1437539-1_E.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_9-1437539-1_E.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_9-1437539-1_E.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[DIP Sockets Quick Reference Guide \(EN\)](#)

English

Product Environmental Compliance

[Product Compliance](#)

English

[Product Compliance](#)

English