91549-1 ~ ACTIVE

AMP

TE Internal #: 91549-1 Portable Crimp Tools, Premium Crimp Tooling, Not Releasable, Not Adjustable, Fixed In Tool, TE Product Specification (114-) View on TE.com >



Application Tooling > Portable Crimp Tools



Tool Grade: Premium Crimp Tooling Ratchet Configuration: Not Releasable, Not Adjustable Die Sets Type: Fixed In Tool Specification Type: TE Product Specification (114-) TE Certification: Yes – Certificate Included

Features

Other

Crimp Form-Wire Barrel Type

Tool Grade

Ratchet Configuration

Die Sets Type

Open Barrel - F Crimp

Premium Crimp Tooling

Not Releasable, Not Adjustable

Fixed In Tool

Specification Type

TE Certification

Power Technology Type

Tooling Type

TE Product Specification (114-)

Yes – Certificate Included

Battery, Electric, Manual

CERTI-CRIMP II, Straight Action Hand Tool

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2016 (169) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content

91549-1

Portable Crimp Tools, Premium Crimp Tooling, Not Releasable, Not Adjustable, Fixed In Tool, TE Product Specification (114-)



Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



		Phosphor Bronze, Signal, Size 20	Signal, Size 20
TE Part # 1-66682-3	TE Part # 66682-1	TE Part # 66683-1	
20 DF PIN PLATED	20 DF PIN STMPD	20 DF SOC. CONT STAMPED	

Customers Also Bought



91549-1

Portable Crimp Tools, Premium Crimp Tooling, Not Releasable, Not Adjustable, Fixed In Tool, TE Product Specification (114-)







Documents

Datasheets & Catalog Pages CERTI-CRIMPII-Premium-August-1-1773864-7

English

Signal Contacts

English

AMPLIMITE Subminiature D Connectors - Cable Connectors

English

CERTI-CRIMP II TOOL DATA SHEET AMPLIMITE CONTACT FAMILY

English

Crimp Term Whitepaper-Use the Right Tool 1-1773953-1

English

Bottoming Dies

English

CRIMPING WHERE FORM MEETS FUNCTION

English

Instruction Sheets Instruction Sheet (U.S.)

English