




Raychem | Raychem Versafit V2

TE Internal #: 674983J001

Raychem Versafit V2, Heat Shrink Tubing, Black, Single Wall Type, 7.6 Expanded Inside Diameter (Min) .299 Expanded Inside Diameter (Min)

[View on TE.com >](#)

Heat Shrink Tubing



Primary Product Color: **Black**

Wall Type: **Single**

Expanded Inside Diameter (Min): **7.6 mm [ .299 in ]**

Recovered Inside Diameter (Max): **3.51 mm [ .138 in ]**

Shrink Ratio: **2:1**

## Features

### Product Type Features

Product Family	V2
Wall Type	Single

### Electrical Characteristics

Voltage (Max)	.6 kV
---------------	-------

### Body Features

Primary Product Color	Black
Shrink Ratio	2:1
Primary Product Material	Irradiated Modified Polyolefin
Flexibility	Very Flexible

### Dimensions

Recovered Wall Thickness (Tolerance)	.56 mm[.022 in]
Expanded Inside Diameter (Min)	7.6 mm[.299 in]
Recovered Inside Diameter (Max)	3.51 mm[.138 in]

### Usage Conditions

Fluid Resistance	None
Shrink Temperature (Min)	70 °C
Heat Shrink Tubing Flammability	Highly Flame-Retardant
Operating Temperature Range	-30 – 125 °C



Heat Shrink Tubing Resistance	Strain, Wrinkling
Recovery Temperature	90 °C

**Product Availability**

Applicable Region	Global
-------------------	--------

**Packaging Features**

Packaging Method	Spool
------------------	-------

**Other**

Meets Low Outgassing Requirements	No
Product Source	China, US

**Product Compliance**

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

**Compatible Parts**




TE Part # CJ2087-000  
HL2010E-KIT-120V



TE Part # EG1114-000  
CV1981-ST-230V1600W-EU

### Also in the Series | Raychem Versafit V2



Heat Shrink Tubing(37)

### Customers Also Bought



TE Part #1-178802-7  
DYNAMIC 3100 REC AND TAB HSG




TE Part #1-353717-2  
DYNAMIC 3000 CONTACT



TE Part #1-917808-2  
DYNAMIC 5000 REC AND TAB HSG




TE Part #1-1903131-0  
DYNAMIC 1200 REC AND TAB HSG




TE Part #1473562-4  
RITS CONN. PLUG ASSY 4P YELLOW




TE Part #1747498-2  
DYNAMIC 4000 REC AND TAB CONT




TE Part #115607J001  
V2-12.0-0-FSP-SM



TE Part #137963J001  
V2-1.5-0-SP-SM



TE Part #985923J001  
V2-6.0-0-SP-SM



TE Part #080745J001  
V2-1.0-0-SP-SM



## Documents

### Datasheets & Catalog Pages

[VERSAFIT V2 Pages from 9-1773447-9](#)

English

[Application Tooling for Raychem Heat Shrink Product](#)

English

[Highly Flame-Retardant, Low Recovery Temp., Metric-Sized Heat-Shrinkable Tubing](#)

English

---

### Product Specifications

[Quality Specification](#)

English