

69692-1 ✓ ACTIVE

AMP

TE Internal #: 69692-1

Portable Crimp Tools, Premium Crimp Tooling, Not Releasable,  
Not Adjustable, Fixed In Tool, MIL Spec / TE Product Specification  
(114-)

[View on TE.com >](#)



Application Tooling > Portable Crimp Tools



Tool Grade: **Premium Crimp Tooling**

Ratchet Configuration: **Not Releasable, Not Adjustable**

Die Sets Type: **Fixed In Tool**

Specification Type: **MIL Spec, TE Product Specification (114-)**

TE Certification: **Yes – Certificate Included**

## Features

### Other

|                             |   |
|-----------------------------|---|
| Crimp Form-Wire Barrel Type | Closed Barrel - Confined Crescent         |
| Tool Grade                  | Premium Crimp Tooling                     |
| Ratchet Configuration       | Not Releasable, Not Adjustable            |
| Die Sets Type               | Fixed In Tool                             |
| Specification Type          | MIL Spec, TE Product Specification (114-) |
| TE Certification            | Yes – Certificate Included                |
| Power Technology Type       | Battery, Manual                           |
| Tooling Type                | T Head Hand Tool                          |

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

|   |   |
|---|---|
| EU RoHS Directive 2011/65/EU                  | Out of Scope  |
| EU ELV Directive 2000/53/EC                   | Out of Scope  |
| China RoHS 2 Directive MIIT Order No 32, 2016 | Not reviewed for China RoHS compliance  |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2021<br>(211)<br>Candidate List Declared Against: JAN 2021<br>(211)<br>Does not contain REACH SVHC |

Halogen Content

Not Yet Reviewed for halogen content













Solder Process Capability

Not applicable for solder process capability

## Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts


|   |  |  |  |
|---|--|--|--|
|  <p>TE Part # 50832<br/>TERMINAL,PIDG PTFE R 22-20 8</p>   |  <p>TE Part # 1-332433-0<br/>TERMINAL,PIDG PTFE R AU 22-20 6</p> |  <p>TE Part # 151439<br/>PIDG 22 RING #6</p>                            |  <p>TE Part # 50832-1<br/>TERMINAL,PIDG PTFE R 22-20 10</p> |
|  <p>TE Part # 50830<br/>TERMINAL,PIDG PTFE R 26-24 6</p>   |  <p>TE Part # 50831<br/>TERMINAL,PIDG PTFE R 22-20 4</p>         |  <p>TE Part # 1-332434-0<br/>TERMINAL,PIDG PTFE R AU 22-20</p>          |  <p>TE Part # 151458<br/>TERMINAL R T PIDG NYL AWG 22 #</p> |
|  <p>TE Part # 50831-1<br/>TERMINAL,PIDG PTFE R 22-20 6</p> |  <p>TE Part # 151438<br/>PIDG 22 RING #4</p>                     |  <p>TE Part # 151441<br/>TERMINAL PIDG RING TONGUE 22<br/>AWG BLACK</p> |  <p>TE Part # 50829<br/>TERMINAL,PIDG PTFE, R 26-24 4</p>   |



TE Part # 332434  
TERMINAL,PIDG PTFE R AU 22-20 8



TE Part # 151440  
PIDG 22 RING #8



TE Part # 50830-2  
PIDG STRATO PTFE RING 26-24 10

## Customers Also Bought




TE Part #3-1617033-0  
HFW1230K06M = M39016/6-105M




TE Part #1976593-1  
TOOL, INS, GB QUADRAX SOCKET



TE Part #211137-000  
CTA-0161



TE Part #47823  
HYP8/10 TERMINYL 2AWG DIE SET




TE Part #47821  
HYP8 TERMINYL 6AWG DIE SET



TE Part #YACT20MD05SNV00100  
SQUARE FLANGE RECEPTACLE




TE Part #1583662-2  
HYP10 10FT HOSE



TE Part #48173  
PNEUMATIC SOLIS STRATO 4 HEAD



TE Part #169475-1  
MINI CERTI-LOK III+



TE Part #1477162-1  
187-32C200

## Documents

### Product Drawings

[T-HEAD PIDG STRATO 26-20 ASSY](#)

English

### Datasheets & Catalog Pages

[CERTI-CRIMP II-Premium-August-1-1773864-7](#)

English

[Crimp Term Whitepaper-Use the Right Tool 1-1773953-1](#)

English



### [Bottoming Dies](#)

English

### [CRIMPING WHERE FORM MEETS FUNCTION](#)

English

---

### [Instruction Sheets](#)

[Instruction Sheet \(U.S.\)](#)

English