



Relays, Contactors & Switches > Relays > High Voltage Relays



Contact Voltage Rating: 12 – 900 kVDC

High Voltage Relay Contact Arrangement: 1 Form X, SPST-NO-DM

High Voltage Connection (Coil): Flying Leads

High Voltage Connection (Power): Stud Terminals

Economizer: Without

Features

Product Type Features

RF Rated	No
Product Type	Contactor
Relay Type	High Voltage

Configuration Features

Economizer	Without
Power Switching	Yes

Electrical Characteristics

Contact Voltage Rating	12 – 900 kVDC
High Voltage Relay Voltage (Max)	900 VDC
High Voltage Relay Coil Voltage Rating	110 VDC
High Voltage Relay Contact Switching Voltage (Max)	900

Contact Features

High Voltage Relay Contact Arrangement	1 Form X, SPST-NO-DM
Auxiliary Contacts	With
High Voltage Relay Contact Current Rating	500 A
Contact Base Material	Copper

Termination Features



High Voltage Connection (Coil)	Flying Leads
High Voltage Connection (Power)	Stud Terminals
Termination Style	Stud Terminals

Mechanical Attachment

High Voltage Relay Mounting Type	Bottom
----------------------------------	--------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Hand solderable with lead free solder

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 6-1618390-8
LEV200H4ANA, RELAY SPST-NO

Also in the Series | Kilovac LEV200

DC Contactors(15)

Definite Purpose Contactors(1)

General Purpose Contactors(4)

High Voltage Relays(13)

Customers Also Bought

TE Part #1-1623781-0
Wirewound Resistor: Vertical Mount

TE Part #1-1617004-0
B07D034BC2-0053 = M5757/23-005

TE Part #8-1618278-1
KC-8/12VDC=RELAY, VACUUM, SPDT

TE Part #1-1618002-1
EV200ADANA=RELAY, EV200 SPST-NO

TE Part #1-1617029-1
HFW1130K06 = M39016/6-104L

TE Part #1-2215056-4
ASSY, EXTRACT TL, QSFP28 1X4

TE Part #1-1618002-6
EV200H2ANA=RELAY, SPST-NO W/AUX

TE Part #1-1879808-9
RP 1J 511R 0.1% 15PPM 1K RL

TE Part #1-2176377-3
RQ 0805 178K 0.1% 10PPM 1K RL

TE Part #1-1617037-8
HFW5A1201S501 = HFW5A RELAY



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_9-1618392-2_C.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_9-1618392-2_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_9-1618392-2_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

5-1773450-5_sec7_LEV200

English