



Identification & Labeling > Printable Tubing > HT-SCE HIGH TEMPERATURE SLEEVES



Printable Tubing Type: **Ladder**

Printable Tubing Grade: **High Temperature**

Printable Tubing Shrink Ratio: **2:1**

Primary Product Color: **Black**

Markers per Sleeve: **1**

[All HT-SCE HIGH TEMPERATURE SLEEVES \(55\)](#)

Features

Product Type Features

Printable Tubing Type	Ladder
Printable Tubing Grade	High Temperature

Body Features

Printable Tubing Shrink Ratio	2:1
Primary Product Color	Black
Markers per Sleeve	1

Dimensions

Product Length	50 mm[2 in]
Supplied Inner Diameter	12.7 mm[.5 in]
Recovered Inside Diameter	6.3 mm[.25 in]
Compatible Cable Diameter Range	6.6 – 11.4 mm[.26 – .449 in]

Usage Conditions

Operating Temperature Range	-55 – 225 °C[-67 – 437 °F]
-----------------------------	----------------------------

Operation/Application

Recommended Ribbon	See TE Document 411-121005 the Printer Product Ribbon Matrix
--------------------	--

Printer/Label Features



Recommended Printer	See TE Document 411-121005 the Printer Product Ribbon Matrix
Printer Technology	Thermal Transfer

Packaging Features

Packaging Quantity	250
--------------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer




This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



 TE Part # 1-2186500-1 T3212-PRINTER	 TE Part # 1-2186502-1 T3224-PRINTER	 TE Part # 1-2186503-1 T3224-SWARE-PRINTER	 TE Part # 154739-000 T300-RIBBON-WH-4HT
 TE Part # CP8122-000 T6112DS-PRINTER	 TE Part # 1-2186501-1 T3212-SWARE-PRINTER		

Customers Also Bought

 TE Part #2398990001 HT-SCE HIGH TEMPERATURE SLEEVES	 TE Part #154739-000 T300-RIBBON-WH-4HT	 TE Part #256157-000 202W342-12-0	 TE Part #YDTS26F11-98SNV001 Straight Plug: D38999, 11-98 Insert, Electroless Nickel Plating
 TE Part #196981-000 362W214-25-0	 TE Part #026831-000 202W302-25-0	 TE Part #161381-000 55PC1131-22-2/4/6-9CS2502	 TE Part #029009N001 202D163-12-20-0-CS6386

Documents

Product Drawings

HT-SCE-1/2-2.0-0

English

Datasheets & Catalog Pages

HT-SCE Heat Shrinkable Sleeves

English

IDENTIFICATION SELECTION GUIDE

English



Product Specifications

[Product Specification](#)

English

Instruction Sheets

[Instruction Sheet \(non U.S.\)](#)

English