

PR-26-REFLECTOR

✓ ACTIVE

Raychem

TE Internal #: 991967-000

Heat Shrink Equipment, Discrete, Worldwide, Cable Assembly,
Reflector, SolderSleeve Products

[View on TE.com >](#)



Application Tooling > Heat Shrink Equipment



Equipment Processing Type: **Discrete**
Heat Shrink Equipment Region: **Worldwide**
Heat Shrink Equipment Application: **Cable Assembly**
Tooling Type: **Reflector**
Spare Parts Tooling Type: **SolderSleeve Products**

Features

Product Type Features

Spare Parts Tooling Type	SolderSleeve Products
--------------------------	-----------------------

Product Availability

Heat Shrink Equipment Region	Worldwide
------------------------------	-----------

Other

Equipment Processing Type	Discrete
Heat Shrink Equipment Application	Cable Assembly
Tooling Type	Reflector

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC



Free





Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts

 TE Part # CAT-R21-731072 Bulbous Heat Shrink Boots: Lipped, Straight	 TE Part # 831991-000 382W042-25/225-0	 TE Part # CAT-R21-7310723 Low Profile Heat Shrink Boots: Poly Molded, Lipped, Straight	 TE Part # CAT-R21-731055422 Heat Shrink Boots: Poly Mold, Lipped
 TE Part # CAT-R21-73107237 Heat Shrink Boots: Lipped, Straight	 TE Part # F20649-000 382A012-100-G05/86-0	 TE Part # 975754-000 202K232-25-01/225-0	 TE Part # CV1995-000 203W301-100-G02/86-0
 TE Part # 823662-000 382A012-3-04/42-0	 TE Part # CAT-R21-7310554 Heat Shrink Boots: Lipped, Right Angle	 TE Part # CAT-R21-73106549 Bulbous Heat Shrink Boots: Lipped, Right Angle	 TE Part # CAT-R21-73105542 Rectangular Heat Shrink Boots: Non Lipped, Right Angle

PR-26-REFLECTOR

Heat Shrink Equipment, Discrete, Worldwide, Cable Assembly, Reflector, SolderSleeve Products





TE Part # CAT-R21-731055

Low Profile Heat Shrink Boots: Poly Mold, Lipped, Right Angle



TE Part # CZ1866-000

302A821-4/86-OCS1821



TE Part # EK7266-000

202S121-25C/86-0



TE Part # EK7270-000

202S132-100C/86-0



TE Part # EK7272-000

202S132-25C/86-0



TE Part # EK7275-000

202S142-100C/86-0



TE Part # EM4332-000

202S142-25C/86-0



TE Part # EK7279-000

202S152-100C/86-0

Customers Also Bought



TE Part #070440-000

STD SNAP-ON MARKERS



TE Part #YDTS26W25-37SBV001

D38999: Straight Plug, 25-37 Insert



TE Part #1803111-1

CRIMPER, INSULATION OVERLAP PREMIUM



TE Part #2150203-1

OCEAN_2.0_APPLICATOR-E-070F120F



TE Part #2151767-1

OCEAN_2.0_APPLICATOR-S-062F090O



TE Part #2836545-2

OCEAN_2.0_APPLICATOR-S-042F050O



TE Part #113069-000

PR-51-REFLECTOR



TE Part #0989072006

RBK-ILS-125-NR2-0-STK



TE Part #1-528015-6

PISTOL GRIP HANDLE

Documents



Product Drawings

PR-26-REFLECTOR

English

Datasheets & Catalog Pages

RAYCHEM_TUBING_CATALOG_SEC2_APPLICATION_EQUIPMENT

English

Raychem Application Tooling

English