




Cable Assemblies > Data Bus Components > Data Bus Couplers



Coupler Type: **In-Line Microcoupler**
Number of Stubs: **2**
Eyelet: **Without**
Data Bus Coupler Cable Length: **9144 mm [360 in]**

Features

Product Type Features

Product Type	Data Bus Component
Cable Type	10612 (Single Optimized Shield Cable)
Coupler Type	In-Line Microcoupler

Configuration Features

Design	With Internal Terminator
Number of Stubs	2
Eyelet	Without

Termination Features

Connection Type	Solder
-----------------	--------

Dimensions

Data Bus Coupler Cable Length	9144 mm[360 in]
-------------------------------	-----------------

Usage Conditions

Operating Temperature (Max)	150 °C
-----------------------------	--------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold






















EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUL 2019 (201) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts

 TE Part # 042871-000 DK-621-0440-4P	 TE Part # 143981-000 DK-621-0434-1S	 TE Part # 241251-000 DK-621-0440-4S	 TE Part # 638491-000 DK-621-0434-1P
 TE Part # 633671-000 DK-621-0433-1S	 TE Part # 118345-000 DK-621-0412-P	 TE Part # 014939-000 DK-621-0439-4S	 TE Part # 191045-000 DK-621-0411-S

			
TE Part # 503123-000 DK-621-0412-S	TE Part # 390299-000 DK-621-0439-4P	TE Part # 902973-000 DK-621-0411-P	TE Part # 449453-000 D-150-0708-5
			
TE Part # 724447-000 DK-621-0435-2S	TE Part # 530805-000 DK-621-0436-2P	TE Part # 704201-000 DK-621-0438-3S	TE Part # 734989-000 DK-621-0437-3S
			
TE Part # 070351-000 DK-621-0435-2P	TE Part # 652913-000 DK-621-0437-3P	TE Part # 349147-000 D-500-0463-612	TE Part # 383392-000 DK-621-0438-3US

Customers Also Bought

			
TE Part #606375N002 Low Profile Heat Shrink Boots: Poly Molded, Lipped, Straight	TE Part #813969-000 Heat Shrink Boots: Non Lipped, Straight	TE Part #811273-000 Low Profile Heat Shrink Boots: Poly Mold, Lipped, Right Angle	TE Part #YACT26JJ04HAV00100 Straight Plug D38999, J04 Insert
			
TE Part #980667-000 D-500-0455-1-612-360	TE Part #5-1617808-1 TD228-1803P=TDFO 10 SEC M83726 /28-1803P	TE Part #591877-3 TJ DBL SPLICE W/100 OHM RESIS	TE Part #650025-000 D-436-29



Documents

Product Drawings

D-500-0457-2-612-360

English

Datasheets & Catalog Pages

Data Bus Components Brochure

English

Product Specifications

Product Specification

English