

D-SCE-1K-3.2-50-9

✓ ACTIVE

TE Internal #: A36937-000

Printable Tubing, Ladder Printable Tubing Type, Fluid Resistant
Printable Tubing Grade, 3:1 Printable Tubing Shrink Ratio, White,
Markers per Sleeve 1

[View on TE.com >](#)



Identification & Labeling > Printable Tubing > D-SCE FLUID RESISTANT SLEEVES



Printable Tubing Type: **Ladder**

Printable Tubing Grade: **Fluid Resistant**

Printable Tubing Shrink Ratio: **3:1**

Primary Product Color: **White**

Markers per Sleeve: **1**

[All D-SCE FLUID RESISTANT SLEEVES \(43\)](#)

Features

Product Type Features

Printable Tubing Type	Ladder
Printable Tubing Grade	Fluid Resistant

Body Features

Printable Tubing Shrink Ratio	3:1
Primary Product Color	White
Markers per Sleeve	1

Dimensions

Product Length	50 mm[2 in]
Supplied Inner Diameter	3.2 mm[.125 in]
Recovered Inside Diameter	1 mm[.043 in]
Compatible Cable Diameter Range	1.1 – 2.6 mm[.044 – .105 in]

Usage Conditions

Operating Temperature Range	-75 – 135 °C[-103 – 275 °F]
-----------------------------	-----------------------------

Operation/Application

Recommended Ribbon	See TE Document 411-121005 the Printer Product Ribbon Matrix
--------------------	--



Printer/Label Features

Recommended Printer	See TE Document 411-121005 the Printer Product Ribbon Matrix
Printer Technology	Thermal Transfer

Packaging Features

Packaging Quantity	1000
--------------------	------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-2186500-1
T3212-PRINTER

TE Part # 1-2186502-1
T3224-PRINTER

TE Part # 1-2186503-1
T3224-SWARE-PRINTER

TE Part # CP8122-000
T6112DS-PRINTER

TE Part # 311292-000
TMS-RJS-RIBBON-4DSCE

TE Part # F55931-000
1966-RIBBON

TE Part # 1-2186501-1
T3212-SWARE-PRINTER

TE Part # 1-2186538-1
RIB-1982-300-110-L-0

TE Part # 1-2186540-1
RIB-1982-300-60-L-0

TE Part # 1-2186549-1
RIB-1982-240-110-L-0-T200

Customers Also Bought

TE Part #3-520408-2
ULTRA-FAST 250 ASY REC 16-14 AWG TPBR

TE Part #1-1586362-6
16P MINI UMNL SEAL,DIE CUT

TE Part #141462-1
PIDG SHUR PLUGS


TE Part #130102
TERMINAL PLAS-GRP RNG-TNG 5MM

TE Part #2-927771-1
TIMER, RECEPTACLE AND TAB

TE Part #2-1856387-9
PGC 1,5-4 (C=6,3mm) Rouge

TE Part #ZPF000000000134010
DMC-MD 26 F

TE Part #1-1586359-6
16P MINIMUMNL GANG WIRE SEAL DR



Documents

Product Drawings

D-SCE-1K-3.2-50-9

English

Datasheets & Catalog Pages

D-SCE Heat Shrink Identification Sleeves

English

IDENTIFICATION SELECTION GUIDE

English

Product Specifications

Product Specification

English

Instruction Sheets

Instruction Sheet (non U.S.)

English