



Identification & Labeling > Labels > Standard Labels > HM HIGH TACK METALIZED POLYESTER LABELS



Label Type: Industrial Label

Label Style: Die-Cut

Label Adhesive Type: High Tack Acrylic Adhesive

UL Listed: Yes

Label Width: 25.4 mm [1 in]

All HM HIGH TACK METALIZED POLYESTER LABELS (36)

Features

Product Type Features

Label Type	Industrial Label
------------	------------------

Body Features

Label Color	Metalized Silver
-------------	------------------

Usage Conditions

Operating Temperature Range	-40 – 150 °C[-40 – 302 °F]
-----------------------------	----------------------------

Printer/Label Features

Number of Labels Across	1
Recommended Printer Ribbon	See Printer Ribbon Matrix
Label Style	Die-Cut
Label Width	25.4 mm[1 in]
Label Height	25.4 mm[1 in]
Label Material	Polyester
Label Thickness	97 Micron

Industry Standards

UL Listed	Yes
-----------	-----

Packaging Features

Packaging Quantity	5000
--------------------	------



Packaging Method	Roll
Other	
Label Adhesive Type	High Tack Acrylic Adhesive

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1-2186500-1 T3212-PRINTER	 TE Part # 1-2186502-1 T3224-PRINTER	 TE Part # 1-2186503-1 T3224-SWARE-PRINTER	 TE Part # 1-2186501-1 T3212-SWARE-PRINTER
---	---	---	---

Customers Also Bought



TE Part #2-1761603-7
IDC LOW PRO HDR 20P VERT BLUE



TE Part #5054134024
RNF-3000 Single Wall Stick Heat Shrink




TE Part #1888654-2
2X8 OFFSET STACK JK



TE Part #165416
P.G.RING DIN



TE Part #5-103955-1
10X2 MTE PIN SR RIBBED .100CL



TE Part #YAFD54-20-39PNC012
RECP ASSY




TE Part #1925249-1
QCM008PC1TT036BC = Circular



TE Part #1925259-1
QCM008SC1TT036PBC = Circular



TE Part #5054552026
RNF-100-1/2-GN-STK



TE Part #1546163-1
M.D. END SECTION,FLAT BASE

Documents

Product Drawings

HM-508254-5-8A

English

Datasheets & Catalog Pages

IDENTIFICATION SELECTION GUIDE

English

HM High Tack Metalized Polyester labels

English

Product Environmental Compliance

TE Material Declaration

English