

753786-1 ✓ ACTIVE

## AMP

TE Internal #: 753786-1

Portable Crimp Tools, Premium Crimp Tooling, Not Releasable, Not Adjustable, Fixed In Tool, TE Product Specification (114-), Battery / Manual

[View on TE.com >](#)



Application Tooling > Portable Crimp Tools



Tool Grade: **Premium Crimp Tooling**

Ratchet Configuration: **Not Releasable, Not Adjustable**

Die Sets Type: **Fixed In Tool**

Specification Type: **TE Product Specification (114-)**

TE Certification: **Upon Request for Fee**

## Features

### Other

Crimp Form-Wire Barrel Type	Open Barrel - F Crimp
Tool Grade	Premium Crimp Tooling
Ratchet Configuration	Not Releasable, Not Adjustable
Die Sets Type	Fixed In Tool
Specification Type	TE Product Specification (114-)
TE Certification	Upon Request for Fee
Power Technology Type	Battery, Manual
Tooling Type	Double Action Hand Tool

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC



Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

### Compatible Parts



TE Part # 170332-1  
PL 187 RECEPTACLE 18-14 AWG  
PTPBR

### Customers Also Bought



TE Part #170332-1  
PL 187 RECEPTACLE 18-14 AWG  
PTPBR



TE Part #708412-1  
XCT 25-6 EQ



TE Part #1670821-1  
PROTECTION CAP, IPT 70 - 120MM?



TE Part #2-1633927-2  
ANVIL



TE Part #2031243-1  
SDE PEW 12 TL & DIE MIC 1



TE Part #5-1633138-1  
ANVIL, COMBINATION



TE Part #HC5957  
BATT. LEAD 90 DEG 70MM-VE.



TE Part #117800-000  
RMW-25/8-1000/ADH-0



TE Part #579490-000  
RMW-50/16-1000/ADH-0



TE Part #2177786-2  
7POS, MIXED,HSG, IEC62196-2 TYPE  
2,BK

## Documents

### Product Drawings

[DAHT 187 POS LOCK 18-14 ASSY](#)

Japanese

### Datasheets & Catalog Pages

[CERTI-CRIMP II-Premium-August-1-1773864-7](#)

English

[1654742\\_HOUSEHOLD\\_APPLIANCES\\_RAST5](#)

English

[Crimp Term Whitepaper-Use the Right Tool 1-1773953-1](#)

English

### Bottoming Dies

English

[CRIMPING WHERE FORM MEETS FUNCTION](#)

English

### Product Specifications

[Application Specification](#)

English

### Instruction Sheets

[DOUBLE ACTION HAND TOOL FOR POSITIVE LOCK REC. CONTACT](#)

Japanese

[Instruction Sheet \(non U.S.\)](#)

Japanese