



Identification & Labeling > Printable Tubing



Printable Tubing Type: **Ladder**

Printable Tubing Grade: **Fluid Resistant**

Printable Tubing Shrink Ratio: **3:1**

Primary Product Color: **Yellow**

Markers per Sleeve: **1**

## Features

### Product Type Features

Printable Tubing Type	Ladder
Printable Tubing Grade	Fluid Resistant

### Body Features

Printable Tubing Shrink Ratio	3:1
Primary Product Color	Yellow
Markers per Sleeve	1

### Dimensions

Product Length	25.4 mm[1 in]
Supplied Inner Diameter	9.53 mm[.375 in]
Recovered Inside Diameter	3.17 mm[.125 in]
Compatible Cable Diameter Range	3.47 – 8.12 mm[.137 – .32 in]

### Usage Conditions

Operating Temperature Range	-75 – 135 °C[-103 – 275 °F]
-----------------------------	-----------------------------

### Operation/Application

Recommended Ribbon	See TE Document 411-121005 the Printer Product Ribbon Matrix
--------------------	--

### Printer/Label Features

Recommended Printer	See TE Document 411-121005 the Printer Product Ribbon Matrix
Printer Technology	Thermal Transfer



## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts

 <p>TE Part # 1-2186500-1 T3212-PRINTER</p>	 <p>TE Part # 1-2186502-1 T3224-PRINTER</p>	 <p>TE Part # 1-2186503-1 T3224-SWARE-PRINTER</p>	 <p>TE Part # CP8122-000 T6112DS-PRINTER</p>
--	--	--	---



TE Part # 311292-000  
TMS-RJS-RIBBON-4DSCE



TE Part # F55931-000  
1966-RIBBON



TE Part # 1-2186501-1  
T3212-SWARE-PRINTER



TE Part # 1-2186538-1  
RIB-1982-300-110-L-0



TE Part # 1-2186540-1  
RIB-1982-300-60-L-0



TE Part # 1-2186549-1  
RIB-1982-240-110-L-0-T200

### Customers Also Bought




TE Part #1622820-2  
SMD Power Resistor: 1 Watt, 3520 Series



TE Part #130014  
PG R 22-16 5MM



TE Part #2042202-1  
Jumper, crown socket, size #2, #4 AWG



TE Part #2-1879642-7  
H8 50K 0.1% 50PPM



TE Part #265725-000  
D-146-0230



TE Part #213841-5  
POWERBAND CONTACTS




TE Part #282039-017  
44A0111-22-9



TE Part #1437623-7  
KS700B1/4=KNOB BLK W/SKIRT 1/4



TE Part #ZPF000000000121739  
182-0862-22



TE Part #1443870001  
D-SCE-12-50-4

### Documents



### Product Drawings

[D-SCE-9.5-50-4](#)

English

---

### Product Specifications

[Product Specification](#)

English

---

### Instruction Sheets

[Instruction Sheet \(non U.S.\)](#)

English