

QS1500-NO.1-F5-0-75MM

✓ ACTIVE

Raychem | Raychem QS1500

TE Internal #: 774185P018

Raychem QS1500, Heat Shrink Tubing, Black, Dual Wall Type, 5.72 Expanded Inside Diameter (Min) .225 Expanded Inside Diameter (Min)

[View on TE.com >](#)



Heat Shrink Tubing



Primary Product Color: **Black**

Wall Type: **Dual**

Expanded Inside Diameter (Min): **5.72 mm [.225 in]**

Recovered Inside Diameter (Max): **1.3 mm [.051 in]**

Shrink Ratio: **4:1**

Features

Product Type Features

Product Family	QS1500
Wall Type	Dual

Electrical Characteristics

Voltage (Max)	.6 kV
---------------	-------

Body Features

Fluid Type	Water
Primary Product Color	Black
Shrink Ratio	4:1
Primary Product Material	Irradiated Modified Polyolefin
Flexibility	Flexible

Dimensions

Recovered Wall Thickness (Tolerance)	1.2 mm[.047 in]
Cut Length	75 mm[2.953 in]
Expanded Inside Diameter (Min)	5.72 mm[.225 in]
Recovered Inside Diameter (Max)	1.3 mm[.051 in]
Heat Shrink Tubing Size Range	1.3 – 5.72 mm[.051 – .225 in]

Usage Conditions

Shrink Temperature (Min)	70 °C
--------------------------	-------



Heat Shrink Tubing Flammability	Flame-Retardant
Operating Temperature Range	-40 – 110 °C
Heat Shrink Tubing Resistance	Abrasion
Recovery Temperature	121 °C

Product Availability

Applicable Region	Global
-------------------	--------

Packaging Features

Packaging Method	Box
------------------	-----

Other

Meets Low Outgassing Requirements	No
Product Source	Czech Republic

Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Also in the Series | Raychem QS1500



Heat Shrink Tubing(37)

Customers Also Bought



TE Part #108961-000
D-406-0003



TE Part #107129-000
Heat Shrink Boots: Non Lipped, Straight



TE Part #HDP26-24-9SN
DEUTSCH HDP20 HOUSINGS



TE Part #1674932-3
TH/.025 CONNECTOR SYSTEM, HOUSING



TE Part #2-1924067-0
MCON, CONNECTOR HOUSING




TE Part #179967-2
MULTILOCK, RECEPTACLE AND TAB



TE Part #184373-1
CONTACT, RECEPTACLE, .070 TYPE



TE Part #170268-2
FF 375 REC 6-10MM2 TPBR



TE Part #175979-2
FF 187 PLUG HSG 8P NYLON BLACK



TE Part #1394684-1
LEVEL FOR 62P

Documents

Product Drawings
QS1500-NO.1-F5-0-75MM

English

Datasheets & Catalog Pages
Application Tooling for Raychem Heat Shrink Product

English



Measuring_Single_Wall_Tubing

English

Selecting_Correct_Tubing

English

Product Specifications

Quality Specification

English

Product Environmental Compliance

Safety Datasheet

Safety Datasheet

German

Safety Datasheet

English

Safety Datasheet

English

Safety Datasheet

English

Safety Datasheet

English

Safety Datasheet

Safety Datasheet

Safety Datasheet

French

Safety Datasheet

Safety Datasheet

Safety Datasheet

Safety Datasheet