



Wire Protection & Management > Heat Shrink Molded Shapes > Cable Transitions & Breakouts



Number of Branches/Legs: 3
Material Code: 3
Breakout & Transition Material Systems Code: 10
Adhesive Pre-Coat: No
Operating Temperature Range: -55 – 200 °C [-67 – 392 °F]

Features

Configuration Features

Number of Branches/Legs	3
-------------------------	---

Body Features

Material	Modified Polyolefin
Material Code	3
Breakout & Transition Material Systems Code	10
Adhesive Pre-Coat	No

Usage Conditions

Operating Temperature Range	-55 – 200 °C[-67 – 392 °F]
-----------------------------	----------------------------

Operation/Application

Power Cable Accessory	No
-----------------------	----

Industry Standards

Government Qualified	No
----------------------	----

Other

Breakout & Transition Adhesive Type	Adhesive Purchased Separately
Comment	Heavy Duty

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought

TE Part #206151-1
CPC SERIES 1

TE Part #165049
PIDG FORMED WIRE PINS

TE Part #320570
PIDG BUTT SPLICES

TE Part #46121
DAHT PG PIDG 26-22 ASSY

TE Part #91517-1
CCII FEMALE MOD IV REC 24-22 ASSY


TE Part #34865
SPLICE,CE 22-10

TE Part #2-323682-1
PIDG RING TONGUE TERMINALS

TE Part #46750-2
HYP8 AMPPOWER 4/0AWG DIE SET



TE Part #242489-000
[CWT-3811](#)



TE Part #166645-1
[EXTRACTION TOOL](#)

Documents

- [Datasheets & Catalog Pages](#)
[1654025_Sec3_HeatShrinkableTubing](#)
English
- [Raychem Molded Parts Visual Guide](#)
English