

D-150-C-12 ✓ ACTIVE

Raychem

TE Internal #: CX2096-000

Sealing Sleeves, Heat Shrink Repair Sleeve, Adhesive Inside Diameter .066 in [1.68 mm], Sleeve Inside Diameter .108 in [2.74 mm], Red

[View on TE.com >](#)



Wire Protection & Management > Heat Shrink Molded Shapes > Sealing Sleeves



Sealing & Repair Sleeve Product Type: **Heat Shrink Repair Sleeve**

Adhesive Inside Diameter: **1.68 mm [.066 in]**

Sleeve Inside Diameter: **2.74 mm [.108 in]**

Sealing & Repair Sleeve Color: **Red**

Wire Size: **22 – 20 AWG**

Features

Product Type Features

Sealing & Repair Sleeve Product Type	Heat Shrink Repair Sleeve
--------------------------------------	---------------------------

Body Features

Sealing & Repair Sleeve Color	Red
-------------------------------	-----

Dimensions

Conductor Outside Diameter	1.1 – 1.5 mm [.043 – .059 in]
Adhesive Inside Diameter	1.68 mm [.066 in]
Sleeve Inside Diameter	2.74 mm [.108 in]
Wire Size	22 – 20 AWG
Cut Length	19.05 mm [.75 in]
Adhesive Cut Length	21.59 mm [.85 in]

Usage Conditions

Operating Temperature Range	-65 – 150 °C
-----------------------------	--------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JAN 2021 (211)

Candidate List Declared Against: JAN 2021 (211)

Does not contain REACH SVHC

Halogen Content

BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CJ2087-000
HL2010E-KIT-120V


Customers Also Bought




TE Part #193495-000
D-150-0179



TE Part #1841-1-5620
CONT PIN



TE Part #218560-001
22759/34-01-9



TE Part #218434-000
22759/41-14-9



TE Part #YDTS24W25-20SNV001
Jam Nut: D38999, 25-20 Insert



TE Part #277151-7
TERMINAL,COPALUM R 1/0 5/16



TE Part #2560-218-2031
CONT PIN



TE Part #1958038-1
COPALUM R 2/0AL 3/8 90 DEG



TE Part #182177-000
55PC1111-22-9-9CS2606



TE Part #1616132-1
QR50H (FAA/PMA)=RELAY

Documents

Product Drawings

[D-150-C-12](#)

English

Datasheets & Catalog Pages

[1654025_Sec8_D-150_D-500_DK-621](#)

English

[Harness Repair Products Quick Reference Guide](#)

English

Product Specifications

[Side Entry Insulation Damage Repair Sleeve \(SEIDRS\)](#)

English

[Installation Procedure for Series D-150-C-1X. Side Entry Insulation Damage Repair Sleeve \(SEIDRS\)](#)

English