

VERSAFIT-KIT-2-COLOR

✓ ACTIVE

Raychem

TE Internal #: D54859-000

Heat Shrink Tubing, Blue / White / Red, Single Wall Type, 2:1 Shrink Ratio, Irradiated Modified Polyolefin, Highly Flame-Retardant, Box

[View on TE.com >](#)



Heat Shrink Tubing



Primary Product Color: Black, Blue, Clear, Green, Red, White, Yellow

Wall Type: Single

Shrink Ratio: 2:1

Primary Product Material: Irradiated Modified Polyolefin

Heat Shrink Tubing Flammability: Highly Flame-Retardant

Features

Product Type Features

Product Family	VERSAFIT
Wall Type	Single

Electrical Characteristics

Voltage (Max)	.6 kV
---------------	-------

Body Features

Material Systems Code	10
Fluid Type	Aviation Fuel, Chemicals/Solvents, De-Icing Fluid, Hydraulic Fluid, Lubricating Oil, Water
Primary Product Color	Black, Blue, Clear, Green, Red, White, Yellow
Shrink Ratio	2:1
Primary Product Material	Irradiated Modified Polyolefin
Flexibility	Very Flexible

Dimensions

Cut Length	152.4 mm[6 in]
Recovered Wall Thickness (Nominal)	1.14 mm[.045 in]

Usage Conditions

Fluid Resistance	Splash Protection
Shrink Temperature (Min)	70 °C



Heat Shrink Tubing Flammability	Highly Flame-Retardant
Operating Temperature Range	-55 – 135 °C
Heat Shrink Tubing Resistance	Fluids, Strain, Wrinkling
Recovery Temperature	90 °C

Product Availability

Applicable Region	Global
-------------------	--------

Packaging Features

Packaging Method	Box
------------------	-----

Other

Meets Low Outgassing Requirements	No
Product Source	UK, US

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts



TE Part # CJ2087-000
[HL2010E-KIT-120V](#)




TE Part # EG1114-000
[CV1981-ST-230V1600W-EU](#)


Customers Also Bought




TE Part #1658643-1
[D-Sub Crimp Recpt Signal 9 Posn, Socket Size 20, Shell Size 1](#)



TE Part #1879447-6
[Wirewound Resistor: Mineral, 2.5 Kw](#)



TE Part #1-282834-0
[TERMI-BLOK PCB MOUNT, 90 10P.](#)



TE Part #2032440-1
[C/A, UMCC TO SMA BHD JACK, 1.37 MM L200MM](#)



TE Part #2-825433-0
[MOD 2 PINHDR 1X20P.](#)



TE Part #1-1609112-2
[CORCOM C SERIES IEC UNFILTERED INLETS](#)



TE Part #169750-000
[S02-09-R](#)



TE Part #1-87230-3
[26 MODII HDR DRRA UNSHRD .100](#)



TE Part #MS580302BA01-60
[MS5803-02BA W GEL P-CAPS T&R](#)

Documents

[Datasheets & Catalog Pages](#)

[Tubing Kits Pages from 9-1773447-9](#)

English

[Application Tooling for Raychem Heat Shrink Product](#)

English



Product Specifications

Quality Specification

English

Product Environmental Compliance

Safety Datasheet

Safety Datasheet

German

Safety Datasheet

English

Safety Datasheet

English

Safety Datasheet

English

Safety Datasheet

English

Safety Datasheet

Safety Datasheet

Safety Datasheet

French

Safety Datasheet

Safety Datasheet

Safety Datasheet

Safety Datasheet