




Wire Protection & Management > Heat Shrink Molded Shapes > Cable Transitions & Breakouts



Molded Part Shape: **Y Shape**
Number of Branches/Legs: **3**
Material Code: **3**
Breakout & Transition Material Systems Code: **10**
Adhesive Pre-Coat: **Yes**

Features

Product Type Features

Molded Part Shape	Y Shape
Size Code	042

Configuration Features

Number of Branches/Legs	3
-------------------------	---

Body Features

Material	Semi-Rigid Modified Polyolefin
Material Code	3
Breakout & Transition Material Systems Code	10
Adhesive Pre-Coat	Yes

Dimensions

Inside Diameter Range (Leg 2)	4 – 9 mm[.16 – .35 in]
Inside Diameter Range (Body)	8 – 20 mm[.31 – .79 in]
Inside Diameter Range (Leg 1)	4 – 9 mm[.16 – .35 in]

Usage Conditions

Operating Temperature Range	-55 – 135 °C[-67 – 275 °F]
-----------------------------	----------------------------

Operation/Application

Power Cable Accessory	No
-----------------------	----



Industry Standards

Government Qualified	No
----------------------	----

Other

Adhesive Code	42
Molded Part Shape Code	382W
Fluid/Chemical Resistance	Occasional exposure to fluids
Adhesive Options	/42 Precoat
Breakout & Transition Adhesive Type	High Performance Pre-Coat Adhesive
Comment	With Heat Recoverable Screen.

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # EG1118-000
CV1981-ST-120V1600W-US



TE Part # 991967-000
PR-26-REFLECTOR



TE Part # EG1120-000
CV1981-ST-120V1600W-UK



TE Part # EG1115-000
CV1981-ST-230V1600W-CH




TE Part # EG1114-000
CV1981-ST-230V1600W-EU

Customers Also Bought



TE Part #6-1609157-5
CORCOM IH SERIES IEC FILTERED
INLETS



TE Part #423797-000
Heat Shrink Boots: Non Lipped,
Straight



TE Part #300329-000
Heat Shrink Boots: Poly Mold, Lipped



TE Part #1623774-1
C14 180R 2% (LOOSE)




TE Part #1623560-1
CRG1206 1% 750R



TE Part #5054114002
RNF-3000 Single Wall Stick Heat Shrink



TE Part #1623430-1
CRG1206 1% 160K



TE Part #5054144004
RNF-100-1/4-3-SP



TE Part #6039853001
99M0111-16-20



TE Part #YAFD57-14-19SWC012
PLUG ASSY

Documents



Product Drawings

382W042-3/42-0

English

Datasheets & Catalog Pages

1654025_Sec4_-3

English

Raychem Molded Parts Visual Guide

English

Product Specifications

Product Specification

English