

HMM

TE Internal #: E94125-000

HMM, Standard Labels, Industrial Label, Die-Cut Label Style, High Tack Acrylic Adhesive, UL Listed Yes, Label Width 50.8 mm [2 in]

[View on TE.com >](#)



Identification & Labeling > Labels > Standard Labels > HMM HIGH TACK METALIZED POLYESTER LABELS



Label Type: **Industrial Label**

Label Style: **Die-Cut**

Label Adhesive Type: **High Tack Acrylic Adhesive**

UL Listed: **Yes**

Label Width: **50.8 mm [ 2 in ]**

All HMM HIGH TACK METALIZED POLYESTER LABELS (23)

Features

Product Type Features

|            |                  |
|------------|------------------|
| Label Type | Industrial Label |
|------------|------------------|

Body Features

|             |                        |
|-------------|------------------------|
| Label Color | Matte Metalized Silver |
|-------------|------------------------|

Usage Conditions

|                             |                            |
|-----------------------------|----------------------------|
| Operating Temperature Range | -40 – 150 °C[-40 – 302 °F] |
|-----------------------------|----------------------------|

Printer/Label Features

|                            |                           |
|----------------------------|---------------------------|
| Number of Labels Across    | 1                         |
| Recommended Printer Ribbon | See Printer Ribbon Matrix |
| Label Style                | Die-Cut                   |
| Label Width                | 50.8 mm[2 in]             |
| Label Height               | 50.8 mm[2 in]             |
| Label Material             | Polyester                 |
| Label Thickness            | 107 Micron                |

Industry Standards

|           |     |
|-----------|-----|
| UL Listed | Yes |
|-----------|-----|

Packaging Features



|                    |      |
|--------------------|------|
| Packaging Quantity | 3000 |
| Packaging Method   | Roll |

Other

|                     |                            |
|---------------------|----------------------------|
| Label Adhesive Type | High Tack Acrylic Adhesive |
|---------------------|----------------------------|

Product Compliance

For compliance documentation, visit the product page on TE.com>

|   |   |
|---|---|
| EU RoHS Directive 2011/65/EU                  | Compliant   |
| EU ELV Directive 2000/53/EC                   | Compliant   |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold   |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2021 (211)<br>Candidate List Declared Against: JAN 2021 (211)<br>Does not contain REACH SVHC |
| Halogen Content                               | Not Yet Reviewed for halogen content  |
| Solder Process Capability                     | Not applicable for solder process capability  |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-2186500-1  
T3212-PRINTER



TE Part # 1-2186502-1  
T3224-PRINTER



TE Part # 1-2186503-1  
T3224-SWARE-PRINTER



TE Part # 1-2186501-1  
T3212-SWARE-PRINTER

Also in the Series | HMM



Standard Labels(23)

Customers Also Bought



TE Part #1717478-1  
REC. ASSEMBLY 8POS. 2.5MM PITCH  
BATTERY



PITCH BATTERY



TE Part #1717478-2  
REC. ASSEMBLY 8POS. 2.5MM PITCH  
BATTERY



TE Part #1513472-1  
UAM Assembly



TE Part #2176341-1  
CRGCQ 0805 10R 1%



TE Part #2337230-3  
TACT ULTRA TB 3.0X2.0X0.6 240GF



TE Part #1-2186320-1  
T200-PRINTHEAD-HOLDER



TE Part #2040910-1  
DDR2 SO DIMM Sockets



TE Part #C37234-000  
HM HIGH TACK METALIZED  
POLYESTER LABELS



TE Part #1513472-5  
UAM Assembly 360mm cable

Documents

Product Drawings

HMM-508508-3-8A

English

Datasheets & Catalog Pages

HMM High Tack Matte Metalized Polyester

English

IDENTIFICATION SELECTION GUIDE

English

HMM-508508-3-8A

HMM, Standard Labels, Industrial Label, Die-Cut Label Style, High Tack Acrylic Adhesive, UL Listed Yes, Label Width 50.8 mm [2 in]

