



Identification & Labeling > Labels > Standard Labels > CSL SELF LAMINATING POLYESTER LABELS



Label Type: **Self-Laminating**

Label Style: **Die-Cut**

Label Adhesive Type: **Permanent Acrylic Adhesive**

UL Listed: **No**

Label Width: **25 mm [.98 in]**

[All CSL SELF LAMINATING POLYESTER LABELS \(20\)](#)

Features

Product Type Features

Printable Label Height	12.7 mm[.5 in]
Label Type	Self-Laminating

Dimensions

Compatible Cable Diameter (Min)	4 mm[.159 in]
Compatible Cable Diameter (Max)	13.5 mm[.53 in]

Usage Conditions

Operating Temperature Range	-30 – 120 °C[-40 – 248 °F]
-----------------------------	----------------------------

Printer/Label Features

Number of Labels Across	8
Recommended Printer Ribbon	See Printer Ribbon Matrix
Label Style	Die-Cut
Label Width	25 mm[.98 in]
Label Height	55 mm[2.17 in]
Label Material	Polyester
Label Thickness	55 Micron

Industry Standards

UL Listed	No
-----------	----



Packaging Features

Packaging Quantity	40
Packaging Method	Sheet

Other

Label Adhesive Type	Permanent Acrylic Adhesive
---------------------	----------------------------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-2186545-1
WINTOTAL-7-DONGLE

TE Part # 1-2186546-1
WINTOTAL-7-END-USER-LICENCE

Customers Also Bought

TE Part #2-2176070-6
SMD Power Resistor: 2 Watt, 3521 Series

TE Part #1-965641-5
TIMER, CONNECTOR HOUSING

TE Part #F16068-000
HX-SCE LOW FIRE HAZARD SLEEVES

TE Part #1-962821-2
ROUND CONNECTOR SYSTEM, PIN AND SOCKET

TE Part #163307-4
MATE-N-LOK PIN

TE Part #1337771-2
50 OHM COAX BNC STR PLUG STR P

TE Part #1703128-1
8POS MT - EDGE HOUSING

TE Part #160458-3
FF 250 TAB 18-16AWG PB SILVER PL LP

TE Part #1106352-1
HB.6.D

TE Part #1437361-3
185-10=10P 28AWG ST

Documents

Product Drawings

CSL-05525P-9

English

Datasheets & Catalog Pages

CSL and LSR - Self-Laminating Laser Printable Polyester Labels

English

IDENTIFICATION SELECTION GUIDE

English



[Product Specifications](#)

[Manuals & User Guides](#)

English