




Wire Protection & Management > Heat Shrink Molded Shapes > Cable Transitions & Breakouts



Molded Part Shape: **Y Shape**  
Number of Branches/Legs: **4**  
Material Code: **3**  
Breakout & Transition Material Systems Code: **10**  
Adhesive Pre-Coat: **Yes**

Features

Product Type Features

|                   |         |
|-------------------|---------|
| Molded Part Shape | Y Shape |
| Size Code         | 034     |

Configuration Features

|                         |   |
|-------------------------|---|
| Number of Branches/Legs | 4 |
|-------------------------|---|

Body Features

|                                             |                                |
|---------------------------------------------|--------------------------------|
| Material                                    | Semi-Rigid Modified Polyolefin |
| Material Code                               | 3                              |
| Breakout & Transition Material Systems Code | 10                             |
| Adhesive Pre-Coat                           | Yes                            |

Dimensions

|                               |                               |
|-------------------------------|-------------------------------|
| Inside Diameter Range (Leg 2) | 9.7 – 19.3 mm[.38 – .76 in]   |
| Inside Diameter Range (Leg 3) | 9.7 – 19.3 mm[.38 – .76 in]   |
| Inside Diameter Range (Body)  | 18.8 – 38.6 mm[.74 – 1.52 in] |
| Inside Diameter Range (Leg 1) | 9.7 – 19.3 mm[.38 – .76 in]   |

Usage Conditions

|                             |                            |
|-----------------------------|----------------------------|
| Operating Temperature Range | -55 – 135 °C[-67 – 275 °F] |
|-----------------------------|----------------------------|

Operation/Application

|                       |    |
|-----------------------|----|
| Power Cable Accessory | No |
|-----------------------|----|



Industry Standards

|                      |    |
|----------------------|----|
| Government Qualified | No |
|----------------------|----|

Other

|                                     |                                    |
|-------------------------------------|------------------------------------|
| Adhesive Code                       | 42                                 |
| Molded Part Shape Code              | 462A                               |
| Fluid/Chemical Resistance           | Occasional exposure to fluids      |
| Adhesive Options                    | /42 Precoat                        |
| Breakout & Transition Adhesive Type | High Performance Pre-Coat Adhesive |

Product Compliance

For compliance documentation, visit the product page on TE.com>

|                                               |                                                                                                                               |
|-----------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                     |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                     |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                       |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2021 (211)<br>Candidate List Declared Against: JAN 2021 (211)<br>Does not contain REACH SVHC |
| Halogen Content                               | Not Low Halogen - contains Br or Cl > 900 ppm.                                                                                |
| Solder Process Capability                     | Not applicable for solder process capability                                                                                  |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CJ2087-000  
[HL2010E-KIT-120V](#)

Customers Also Bought




TE Part #2-1318114-6  
[DYNAMIC 2000 REC AND TAB HSG](#)




TE Part #1-177648-8  
[DYNAMIC 3100 REC AND TAB HSG](#)



TE Part #2-327960-2  
[PIDG RECTANGULAR TONGUE  
TERMINALS](#)




TE Part #158229-000  
[Heat Shrink Boots: Non Lipped,  
Straight](#)



TE Part #212995-000  
[TXR18AB00-2208AI](#)




TE Part #YDTS26W25-37SBV001  
[D38999: Straight Plug, 25-37 Insert](#)



TE Part #1052527-1  
[2052 1215 00](#)



TE Part #1532255-7  
[M83513/10-F02NN = MCKS-N1-B-  
37PRT1A](#)



TE Part #1214-202-0978  
[R SNAP](#)

Documents

Product Drawings

[462A034-3/42-0](#)

English

Datasheets & Catalog Pages

[1654025\\_Sec4\\_-3](#)

English

[Raychem Molded Parts Visual Guide](#)

English





---

**Product Specifications**

[Product Specification](#)

English

---

**Product Environmental Compliance**

[Safety Datasheet](#)

[Safety Datasheet](#)

German

[Safety Datasheet](#)

German

[Safety Datasheet](#)

English

[Safety Datasheet](#)

English

[Safety Datasheet](#)

English

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

French

[Safety Datasheet](#)

French

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)