



Energy & Power > Power Cable Accessories > Separable Connectors > Loadbreak Connections > LOADBREAK 200A INSULATING CAP



Loadbreak Connection Product Availability: **AMERICAS**

Loadbreak Connection Technology: **Cold Applied**

Loadbreak Connection Voltage Class: **≤ 15 kV**

Loadbreak Connection Connector Type: **Compression**

Bushing Type: **200A**

[All LOADBREAK 200A INSULATING CAP \(3\)](#)

Features

Product Type Features

Loadbreak Connection Technology	Cold Applied
Loadbreak Connection Connector Type	Compression
Bushing Type	200A

Electrical Characteristics

Loadbreak Connection Voltage Class	≤ 15 kV
------------------------------------	---------

Body Features

Loadbreak Connection Conductor Material	Aluminum/Copper
---	-----------------

Operation/Application

Application Type	Insulating Cap
------------------	----------------

Industry Standards

UL Rating	No
-----------	----

Product Availability

Loadbreak Connection Product Availability	AMERICAS
---	----------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2018 (191) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



TE Part # CAT-ELB-BI
LOADBREAK BUSHING INSERT



TE Part # CAT-ELB-LRTP
LOADBREAK REDUCING TAP PLUG



TE Part # CAT-ELB-ETP
LOADBREAK ELBOW TAP PLUG

Also in the Series | Raychem ELB



Dead Break Connections(1)



Loadbreak Connections(49)


Customers Also Bought



TE Part #2273023-2
M12 A-CODE FEMALE STRAIGHT PIGTAIL



TE Part #T4111502031-000
M12 Field Installable Unshielded



TE Part #2-282836-8
TERMI-BLOK PCB MOUNT 90 9P Ke



TE Part #1274563-2
PLUG KIT, STRAIGHT, MINI BNC



TE Part #3-535542-0
60 MODIV VRT DR CE 100/130



TE Part #602300-2
AMPACT Wedge Pressure Tap Connectors



TE Part #1727912-3
EP TYPE INSULATED PIERCING CONNECTORS



TE Part #2182442-2
Pin Terminal Connectors



TE Part #5-1415899-2
PCB Power Relay: 12-16 Amp, Monostable



TE Part #198817-000
HVS/HVSR IN-LINE TRANSITION /REDUCER KIT

Documents

Product Drawings

ELB-15-200-IC

English

Datasheets & Catalog Pages

200A INSULATING CAP RAYCHEM

English