




Wire Protection & Management > Heat Shrink Molded Shapes > EMI Shielded Boots



Molded Part Type: **EMI Shielded Molded Parts**
EMI Shielded Boot Color: **Black**
EMI Shielded Boot Material Systems Code: **25**
EMI Shielded Boot Material: **Modified Elastomer**
Adhesive Pre-Coat: **No**

Features

Product Type Features

Product Type	Molded Part
Molded Part Type	EMI Shielded Molded Parts
Angle	Straight

Body Features

Material Code	25
EMI Shielded Boot Color	Black
EMI Shielded Boot Material Systems Code	25
EMI Shielded Boot Material	Modified Elastomer
Adhesive Pre-Coat	No

Dimensions

EMI Shielded Boot Expanded Inside Diameter (Min)	20 mm[.787 in]
EMI Shielded Boot Recovered Inside Diameter (Max)	10.4 mm[.41 in]
EMI Shielded Boot Cable Diameter Range	5.25 – 9.35 mm[.21 – .37 in]

Usage Conditions

Operating Temperature Range	-75 – 150 °C
-----------------------------	--------------

Other

Adhesive Code	86
---------------	----



EMI Shielded Boot Adhesive Type

High Performance Pre-Coat Adhesive

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # EG1118-000
[CV1981-ST-120V1600W-US](#)



TE Part # 991967-000
[PR-26-REFLECTOR](#)



TE Part # EG1120-000
[CV1981-ST-120V1600W-UK](#)




TE Part # EG1115-000
[CV1981-ST-230V1600W-CH](#)



Also in the Series | Raychem Rayaten



Customers Also Bought



Documents

Product Drawings
202S121-25C/86-0

English

Datasheets & Catalog Pages
INSTALITE Molded Boots with Rayaten

English



Product Environmental Compliance

Safety Datasheet

Safety Datasheet

German

Safety Datasheet

English

Safety Datasheet

English

Safety Datasheet

English

Safety Datasheet

Safety Datasheet

French

Safety Datasheet

French

Safety Datasheet

Safety Datasheet

Safety Datasheet

Safety Datasheet